






# GLOBAL INDUSTRIAL LOCKER FEATURES

- Durable powder coat finish
- 6" Legs
- Anchors sold separately
- Available in assembled & unassembled
- Reinforced welded doors and frames
- 15mm or 16 gauge steel doors and frame
- Padlock hasp designed for a 9/32" diameter shackle padlock
- 1 Year warranty
- Coat Rod: Included in single door models 18'D or greater
- Hat Shelf: Included with single door models



	STANDARD LOCKER SERIES			SPECIALTY LOCKER SERIES	
	Capital	Paramount	Infinity	Clear View	Digital
					
<b>Door Handle Type</b>	With or Without Recessed Cup-Pull	Lift Latch	Recessed Handle & Fingertip Lift	Finger Pull Friction Hasp. Recessed Handle & Fingertip Lift	Finger Pull Friction Hasp. Lift Latch & Recessed Cup Pull
<b>Lock Type</b>	Padlock Hasp & Built-in Lock Latch	Padlock Hasp & Built-in Lock Latch	Padlock Hasp & Built-in Lock Latch	Padlock Hasp & Built-in Lock Latch	Padlock Hasp & Built-in Lock Latch
<b>Locking System</b>	1-Point	3-Point	3-Point	1-Point or 3-Point (Depends on Tier)	1-Point or 3-Point (Depends on Tier)
<b>Door Type</b>	Louvered Door, Ventilated Door	Louvered Door	Louvered Door, Ventilated Door	Louvered Door	Louvered Door
<b>Hinge Type</b>	5 Knuckle (Louvered Door), Piano Hinge (ventilated Door)	5 Knuckle (Louvered Door)	5 Knuckle (Louvered Door), Piano Hinge (ventilated Door)	Piano Hinge	5 Knuckle
<b>Configuration</b>	1 & 3 Wide	1 & 3 Wide	1 & 3 Wide	1, 3 & 4 Wide	1 & 3 Wide
<b>Tier Type</b>	1,2-,3-,4-,6-, & 16- Person	1-, 2-, & 3- Tier	1-, 2-, 3-, & 4- Tier	1-, 2-, 3-, 4-, 5, 6 16-Person	1-, 2-, 3-, 4-, & 6- Tier
<b>Color(s)</b>	Gray, Tan, Blue, Dark Gray w/ Ventilated door	Gray, Tan, Blue	Gray, Tan, Blue, Dark Gray w/ Ventilated door	Gray, Tan	Gray, Tan, Blue