

30" High Velocity Fan



YM-Yoke Mount Standard Mounting Options



PS- Pedestal Stroller



CW- Column Wall Mount



PB- Pedestal Base

Shipping Weights: 161 lbs/ 59 kg

147 lbs/ 67 kg

136 lbs/ 62 kg

SIZE	CFM	HP	FAN DIMENSIONS			DISTANCE AIR THROW	SHIPPING WEIGHT
			W	D	I.D.		
30"	12,000	1	37"	22"	30 7/8"	200' / 60 m	125 lbs/ 57 kg

Propeller: 30" Diameter, 2 Blade GalvAlum (15 Degree)

Fan Inlet/Outlet: 14 Gauge Spun Steel

Finger Guards: OSHA Standard, Spiral Wound Steel

RPM: 1800

Decibels: 82.2 @ 20'

Enclosure: TEAO

Frame: 56

Ambient Temperature: 40C

Duty Cycle: Continuous

Power Cord (115V Only): 12' Length

Coverage: 12,000 Sq.Ft. Max

Warranty: 2 Years

Voltage	Motor Amps	Running Amps
115V/ 208-230V	13.4/ 6.8-6.7	12.9/ 6.6-6.5
208-230/460V*	3.6-3.5/ 1.8	3.4-3.3/ 1.7
277V	5.6	5.4

* Standard

30" High Velocity Fan Air Flow Pattern

