

## NEW FULLY WELDED BOTTLE JACKS

- Fully welded base prevents oil leakage over time and improves durability
- Built-in safety valve protects against dangerous ram over-extension
- Air/Hydraulic units feature a powerful pump-free air motor which conveniently lifts ram with simple air controls
- Extension screw adjusts to desired work height for added reach



MODEL	CAPACITY	TYPE	MIN HEIGHT	MAX HEIGHT
4402	2 Ton	Manual	7.1"	13.6"
4404	3 Ton	Manual	7.6"	14.7"
4406	6 Ton	Manual	8.3"	16.3"
4408	8 Ton	Manual	9.1"	18.1"
4410	10 Ton	Manual	9.1"	18.3"
4412	12 Ton	Manual	9.1"	18.3"
4412S	12 Ton Short	Manual	7.5"	14.4"
4412AH	12 Ton	Air / Hydraulic	9.1"	17.6"
4420	20 Ton	Manual	9.5"	17.9"
4420S	12 Ton Short	Manual	7.5"	13.8"
4420AH	20 Ton	Air / Hydraulic	9.5"	18.0"
4430	30 Ton	Manual	10.8"	17.3"
4450	50 Ton	Manual	10.4"	16.7"