PORTACOOL:



APEX 700

PEAK COOLING, INTELLIGENT CONTROL

Introducing the Apex[™] 700, your stylish evaporative cooling solution. This cooler is designed for simplicity and sophistication. With a quiet operation of just 53 dB, it covers areas up to 700 square feet and reaches up to 60 ft. From weddings, events, and cookouts to harsh environments like auto shops, construction, and manufacturing sites, the Apex 700 ensures cool comfort anytime, anywhere. Say goodbye to sweating it out and hello to the cooling power of the Apex 700.

- 1. Smart, Connected Cooling
- 2. Quiet, Efficient, and Far-Reaching
- 3. Rugged, Portable, and Smartly Designed



POWERED BY COOLSYNC™ TECHNOLOGY.

The ultimate evaporative coolers are here. Connectivity powered by CoolSync[™] Technology. Sync your cooler to your smartphone and take total control from anywhere.

- Easily adjust fan speeds
- Control multiple units simultaneously
- Schedule run-times in advance
- Set a timer for the cooling duration

Lifetime warranty on all molded housings. **3vr. *Limited warranty** on motor and

3yr. *Limited warranty on motor and electrical components.



PORTACOOL

POWERFUL & EFFICIENT COOLING:

This chart illustrates the remarkable cooling capabilities of the Apex Series high-velocity evaporative coolers. The Apex 700, designed for cooling spaces up to 700 square feet, creates a refreshing breeze that extends up to 60 feet.



Digital display

CoolSync™_

technology

Improved 8"

Portacool

technology

Frontline_

airflow inlet

with new water_

APEX 700

- **Space Optimization** Achieve maximum cooling without sacrificing space. Our slimmer profile and new front intake allows you to place your Portacool evaporative cooler against any wall.
- **Extended Cooling Reach -**Our high-velocity cooler delivers a refreshing breeze up to 60 ft. away.
- **Digital Louver Control -**The oscillating louvers allow customized airflow to maximize your cooling coverage.
- Whisper Ouiet Performance -The centrifugal blower design and motor combination reduce noise, creating a tranquil cooling environment.

SLIMMER PROFILE



MODEL NUMBER	OPTIMAL COOLING (Sq. Ft.)	VELOCITY (Mph)	AIR FLOW REACH (Ft.)	NOISE (dB)	WATER RESERVOIR (Gallons)	PRODUCT WEIGHT (Without Water)	AIRFLOW (CFM's)	AMP'S	DIMENSIONS (In.)
PACA07001A1	UP TO 700	37	60	53	22	88	1400	4.0	(HEIGHT) 52 (DEPTH) 24 (WIDTH) 27

Lifetime warranty on all molded housings. 3yr. *Limited warranty on motor and electrical components.



www.portacool.com

Portacool parts and accessories are available online at portacool.com or through your local distributor or retail location.

PARMKTLT504 3/04/24