




Compact and easy to use, the Core<sup>®</sup> is unbeatable for value and features. The Core operates smoothly and looks sleek, but it's created for utility. The ABS housing withstands field, classroom and laboratory environments, and the stainless steel pan is removable, making it simple to clean. ShockProtect<sup>®</sup> safeguards the load cell, so it can handle overloads without damage. To help prevent theft, a built-in security slot accommodates an optional Kensington-type lock and cable. Portability is not an issue with the Core, as the balance operates by battery or AC adapter. A convenient weigh-below hook facilitates below-balance weighing for density and specific gravity measurements.

The most durable compact balance in its class, the Core is unmatched in value



## Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Programmable backlight can be set to “always on,” “always off” or “light only when weighing”
- Balances stack efficiently and safely to save space (120mm pan size only)
- Color-coded keys facilitate quick recognition of the most frequently used buttons
- Dual tare keys facilitate operation with either the left or right hand
- Security slot for optional Kensington-type lock and cable to help prevent theft
- Large, grade 304 stainless steel pan allows swift cleaning
- Rugged construction stands up to industrial use
- Three-point ShockProtect<sup>®</sup> feature helps prevent overload damage to internal components
- Hook included for weighing below the balance
- Auto power-off to save energy
- Audible overload alarm warns when capacity has been exceeded
- Zero-tracking feature ensures display returns to zero reading
- Operates with AC adapter (included) or batteries (not included)

## Applications

- Weighing

## About ADAM:

For more than 40 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

Model	CQT 202	CQT 251	CQT 601	CQT 1501	CQT 2000	CQT 2601	CQT 5000
<b>Capacity</b>	200g	250g	600g	1500g	2000g	2600g	5000g
<b>Readability</b>	0.01g	0.1g	0.1g	0.1g	1g	0.1g	1g
<b>Pan Size</b>	4.7" ø / 120mm ø				5.7" ø / 145mm ø		
<b>Weighing Units</b>	g, kg, lb, oz, N, GN, ct, dr, tl,T						
<b>Stabilization Time (sec)</b>	2						
<b>Calibration</b>	External calibration						
<b>Display</b>	Backlit LCD with 0.7"/ 18mm-high digits						
<b>Power Supply</b>	12VAC 150mA adapter / 6 x AA batteries						
<b>Operating Temperature</b>	0° to 40°C / 32° to 104°F						
<b>Housing</b>	ABS plastic						
<b>Draft Shield</b>	Round 5.1" ø x 3.5" / 130mm ø x 90mm				N/A		
<b>Overall Dim.</b>	6.7"x9.8"x3.1" / 171x250x80mm (wxdxh)						
<b>Net Weight</b>	2lb / 0.9kg						

## Accessories

Item number	Description
308002042	Hard carrying case with lock
308232033	In-use wet cover
308232036	In-use wet cover (pack of 5)
308232037	In-use wet cover (pack of 10)
700100046	Kensington-type lock and cable
700660290	Calibration certificate
700100035	M1 1g - 100g calibration weight set Includes case to store weights
700100071	M1 1g - 2kg calibration weight set Includes case to store weights
700100072	M1 200g Calibration Weight
700100060	M1 500g Calibration Weight
700100029	M1 1kg Calibration Weight
700100030	M1 2kg Calibration Weight
700100012	F1 200g Calibration Weight

## Key Accessories



### Kensington-type lock and cable

The security lock and cable fits the built-in lock attachment on balances and scales, and loops around an object to secure your balance in place. The flexible steel cable is difficult to cut, and the combination lock allows users to choose a combination number for added security.



### In-use wet cover

In-use covers provide an easy and affordable way to help keep the balance clean and protected.



### Hard carrying case

Solidly constructed with stainless steel corners, the case contains soft foam cushioning to protect the balance or scale. A shoulder strap is included, and the case is lockable.

Supplied by