



The GBK is designed to stand up to the demands of rigorous industrial applications. With its compact stainless steel platform, the GBK fits easily on a cart or table and is ideal for parts counting, batching or routine weighing. For flexible positioning, the pillar-mounted display can be used without the pillar. Oversized rubber feet offer stability, while the cast aluminum frame provides even weight distribution and ensures consistent readings regardless of where the object is placed during weighing. The GBK's intuitive software helps save time and reduces errors when logging data. Powered by adapter or the built-in, rechargeable battery, GBK operates anywhere. The GBK-aM version is NTEP and Measurement Canada approved.

The best solution for demanding industrial and manufacturing tasks



Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Capacity tracker built into display for easily monitoring possible overloads
- Checkweighing LEDs clearly show under, over and acceptable limits
- Programmable backlight can be set to "always on," "always off" or "light only when weighing"
- Color-coded keys facilitate quick recognition of the most frequently used buttons
- Level indicator and adjustable feet ensure proper balance setup for optimum weighing results
- Large, grade 304 stainless steel pan allows swift cleaning
- RS-232 interface is available to provide speedy connection to computers and printers
- Rugged construction stands up to industrial use
- Sealed keypad protects against dirt and spills
- Overload protection helps prevent damage to internal components
- Checkweighing with audible alarm
- Memory accumulation totals results
- Parts counting with freely selectable sample sizes
- Parts counting optimization automatically refines piece weight as parts are added
- Preset tare function speeds the process of repetitive weighing
- Selectable digital filtering helps minimize effects of vibration and disturbances
- Zero-tracking feature ensures display returns to zero reading
- Rechargeable battery included for operation almost anywhere
- Programmable auto power-off to save energy

Applications

- Weighing
- Parts counting
- Percentage weighing
- Checkweighing
- Dynamic / animal weighing
- Accumulation

About ADAM:

For more than 40 years, professionals worldwide have relied on Adam Equipment for an extensive selection of dependable and affordable weighing equipment. Adam provides the right balance of speed, performance and value.

GBK Bench Checkweighing Scales



Model	GBK 16a	GBK 35a	GBK 70a	GBK 130a	GBK 260a	GBK 15aM	GBK 30aM	GBK 60aM	GBK 150aM	GBK 300aM
Capacity	16lb / 8kg	35lb / 16kg	70lb / 32kg	130lb / 60kg	260lb / 120kg	15lb / 6kg	30lb / 15kg	60lb / 30kg	150lb / 60kg	300lb / 150kg
Readability	0.0002lb / 0.1g	0.001lb / 0.5g	0.002lb / 1g	0.005lb / 2g	0.01lb / 5g	0.002lb / 1g	0.005lb / 2g	0.01lb / 5g	0.02lb / 0.01kg	0.05lb / 0.02kg
Repeatability (S.D.)	0.0004lb / 0.2g	0.002lb / 1g	0.004lb / 2g	0.01lb / 4g	0.02lb / 10g	0.004lb / 2g	0.01lb / 4g	0.02lb / 10g	0.04lb / 0.02kg	0.1lb / 0.04kg
Linearity (+/-)	0.0006lb / 0.3g	0.002lb / 1g	0.004lb / 2g	0.01lb / 4g	0.02lb / 10g	0.004lb / 2g	0.01lb / 4g	0.02lb / 10g	0.04lb / 0.02kg	0.1lb / 0.04kg
Pan Size	11.8"x15.7" / 300x400mm									
Weighing Units	g, kg, lb, lb:oz, oz									
Stabilization Time (sec)	2									
Interface	RS-232									
Calibration	External calibration									
Display	Backlit LCD with 0.8" / 20mm -high digits									
Power Supply	12VDC 800mA adapter / Internal rechargeable battery									
Operating Temperature	-10° to 40°C / 14° to 104°F									
Housing	ABS plastic indicator with die-cast aluminum base									
Overall Dim.	11.8"x20.5"x26.8" / 300x520x680mm (wxdxh)									
Net Weight	16.8lb / 7.6kg									
Approvals	N/A					NTEP / Measurement Canada				

Accessories

Item number	Description
3052010526	In-use wet cover
3074010266	RS-232 cable (Null-Modem)
3074010507	RS-232 to USB adapter (must order corresponding RS-232 cable)
1120011156	ATP thermal printer
3126011263	ATP thermal printer paper
3126011281	ATP thermal printer paper (pack of 10)
600002028	AdamDU data collection program
700200107	Casters / wheels (set of 4)
700660290	Calibration certificate

Key Accessories



ATP thermal printer
Easy-to-use features combined with quick set-up equals a truly versatile thermal printer. A single push-button feed key and three easy-to-read LED indicators make operation simple.



In-use wet cover
In-use covers provide an easy and affordable way to help keep the balance clean and protected.



Casters / Wheels
Optional caster wheels provide easy mobility for bench and floor scales. A brake lock prevents movement during use.

Supplied by

www.adamequipment.com

Adam Equipment follows a policy of continuous improvement and reserves the right to change specification and pricing without notice. Adam Equipment's standard terms and conditions of sale apply. Errors and omissions excepted.