OPTICLUX 10-2 P TX (Wood-Light) D15953100



ENGINEER OF LIGHT.



fitted with LED - Energy efficiency category A+

color rendering index (CRI) > 95 colour temperatur 6500 K

work equipment electronic converter

mains lead 1.8 m (5.9 ft) Hospital Grade plug

lens; dimensions Ø 160 mm lens; diopters 3,5

luminaire body polyamide (PA) weight (net) 2.1 kg (4.6 lb)
Power consumption 12 W

usage keypad at luminaire head

balance of articulation joints spring class of protection II

Accessory roll support, rail fastening with removal protect

table clamp with removal protection, universal fastening with removal protection, extension ar removal protection, wall bracket with removal

protection

norms EN 60601-1, EN 60601-2-41

special features Rotary feedthrough (360° Turnover axis),

scratch-proof plastic lens, continuously dimmal

switchable Wood-Light

Fastening Table Clamp









light distribution





