Workplace-system luminaire WLA 1100/850

113470000-00800170



ENGINEER OF LIGHT.



fitted with

work equipment

connected load power consumption luminous flux luminous efficacy light color color rendering index (CRI) glare-free system of protection class of protection technology usage luminaire body lamp cover

design fastening dimension

weight (net)

mains supply



electronic driver 120-240V: 50/60Hz approx. 15 W approx. 1100 lm approx. 81 lm/W

neutral white, approx. 5000 K

> 80

structured screen

IP 20

switchable rocker switch

aluminium/plastic, anodized, aluminium colored anodized

structured screen approx. 1.7 kg (3.74 lbs) connection box, built-in plug

GST 18i3F REV mounted version screw down lash A=449 mm (17.69")









GST 18i3F REV

illuminance

distance: 100 cm Em: Emax: Emin: 100 cm 80 60 40 20 E [lx]

luminous intensity





