## **LED** machine luminaire

## LUMATRIS - MSAL 48 S 113095000-00596761



I \_\_\_\_

fitted with

work equipment
connected load
power consumption
system of protection
class of protection
technology
usage
luminaire body
material
lamp cover
weight (net)
mains supply

design fastening dimension special features 48 x I FD

daylight white, 5600-6000 K Color Rendering Index (CRI)=80

without 22-26 V; DC approx. 16W

IP 68 - 1m/ IPX9K; DIN 40050-9

Ш

switchable without switch

anodized aluminum glass screen

approx. 5.1 lbs. [2.3 kg] built-in M12 plug

mounted version

mounting rail, tap hole 2xM6

A= 16.5" [420mm]


light forming, connection on the side



M12

## illuminance

measuring conditions: d=100cm



## luminous intensity

