ROCIA.focus - RFF 600/850/D 113183000-00680258



ENGINEER OF LIGHT.



fitted with

work equipment connected load power consumption light distribution beam angle light color color rendering index

(CRI) glare-free system of protection class of protection technology

usage

luminaire body lamp cover tubular sections balance of articulation

joints weight (net) mains lead

optional mounting special features

LED

electronic driver in housing 100-240 V; 50/60 Hz approx. 9.5 W

direct, wide-angled beam

40°

neutral white, approx. 5000 K

> 80 screen IP 65

switchable, continuously dimmable push

button

aluminium, anodized, black

glass screen

flexible metal tube, black

friction

approx. 1.9 kg (4.2 lbs)

approx. 3,2 m (10.5 ft); NEMA 1-15P plug

table clamp (accessory), wall bracket (accessory)

flood with a 40° angle of radiation



NEMA 1-15P

illuminance





