Tube luminaire RL70LE- 24 N 113279000-00712020





fitted with

work equipment connected load power consumption luminous flux luminous efficacy light distribution light colour color rendering index (CRI) system of protection class of protection technology usage luminaire body weight (net) mains supply

fastening dimension light output outside diameter side part special features

Waldmann W

ENGINEER OF LIGHT.

LED Energy efficiency category A+ without 22-26 V; DC approx. 12.5 W approx. 950 lm approx. 79 lm/W direct neutral white, approx. 5000 K > 80 IP 67 III switchable external acrylic approx. 1 kg, 2.2 lb connector ST16/2 BS pipe clamp (accessory) A=370 mm, 14.5 in D= 316 mm, 12.4 in 70 mm, 2.75 in A with screwed cable gland light forming



.

ST16/2 BS


illuminance




10

90°

60



C0-C180 C90-C270 90° 75° C0/KIm 0° 15° 0° 15° 30°



Errors and technical changes excepted. Images can vary from original. Photometric and electrical data may vary due to component tolerances.