

243228-29 Bottom Mount Freezer

Nexel® Refrigerator/Freezer French Door, 16 & 18 cu.ft. Stainless Steel

243229, 18 cu.ft.

243228, 16 cu.ft.



- KEY BENEFITS
- DOE, CSA Listed
 - Electronic Temperature Control
 - LED interior Light
 - Frost Free
 - Fresh Food Compartment
 - 2 Full Glass Shelves
 - 1 Split Glass Shelf for tall items
 - 2 Half Width Crisper Drawers with Humidity Control
 - 6 Half Door Gallon Bins

Bottom Mount Freezer Compartment

- 2 Full Width Plastic Drawers

Weights & Dimensions

	243228	243229	243228	243229
Width	28.32"	32.30"	Height	70"
Depth	29.33"	27.30"	Weight	183 lbs / 202.8 lbs

Product Details

	243228	243229	243228	243229
Body Color Family	Stainless Steel Look		Reversible Door	No
Light	Yes		Number of Level Legs	4
Door Swing	Single		Brand	Nexel
Adjustable Shelf	Yes		Type	Bottom Mount Freezer
Number of Full Door	6		Shelf Type	Adjustable Glass
Shelves Defrost Type	Automatic		Energy Usage	DOE
Number of Shelves	5	6	Handle Type	Recessed door pull
Material	Stainless Steel		Capacity	455L, 16 cu.ft. / 510L, 18 cu.ft.
Door Color Family	Stainless Steel Look		Voltage	120V 60Hz
Number of Crisper	2		Thermostat Type	Electronic
Crisper Drawer Material	GPPS		Refrigerant Type	R600A
Manufacturers Part Number	BCD-455WTE	BCD-510WTE		

Warranty

Warranty	1 yr
----------	------

Compliance & Certifications

Certifications	CSA
----------------	-----

For more information, visit globalindustrial.com or call 1-800-645-1232.

KEY BENEFITS

PRODUCT FEATURES