
GLOBAL™ INDUSTRIAL
We can supply that.®

User's manual	Manual del usuario	Manuel de l'utilisateur
Customer Service US: 1-800-645-2986	Servicio de atención al Cliente US: 1-800-645-2986	Service à la clientèle Canada: 888-645-2986

Digital LED Wall Clock

Model: 282487




MAIN FUNCTIONS

1.Display time hour,minute,date,month,year and week day, 12 hour format(AM: morning , PM: afternoon).

2.Temperature display function: format ℃ /°F changeable.

KEYS SCHEMATIC

1. SET KEY
2. UP KEY ▲
3. DOWN KEY ▼



press SET key to set each parameter in circle turn

OFF → hour → minute → month → date → year → temperature

Remark: press "SET" key, the screen display "OFF" or "ON", then press "▲" or "▼" key to open or close daylight–saving time. When daylight–saving time mode is ON, the time will be set 1 hour ahead.

press key 1 "SET" to be daylight–saving time mode,again press key 1 "SET" into time set status, the hour digits on screen flashing,then press UP key 2 "▲" or DOWN key 3 "▼" to adjust your expected time. Same way to set minute, month, date, year and temperature format(℃/°F). or 50 °F ~ 120 °F

TEMPERATURE FUNCTION:

Measure the environment temperature automatically, range is –10℃ ~ 50℃ (accuracy ± 1℃) or 50 °F ~ 120 °F

POWER & MAINTENANCE

Power by: DC 5V/2A adaptor, Back up batteries: 2* AA batteries. Take away the batteries if you don't use the clock for a long time,to prevent any damage of chemical corrosive liquid. Use a soft cloth to clean the clock's body and keep it dry,put back into its packing box.Don't use any chemical corrosive liquid or clean agent to clean the body.