

GIDICP962



56.63" x 21.5" x 21.75" (H x W x D)

Two-door cycle defrost refrigerator-freezer in slim width and white finish

Highlights:

Unique 21 1/2" width is ideal for small kitchen spaces

Adjustable glass shelves and large crisper drawer for optimum storage

Multiple door racks accommodate condiments and bottles

Product Features:

Thin-line design	Limited space is no problem for our thin-line models, designed specifically for those hard-to-fit spots
Cycle defrost	Combines an automatic defrosting refrigerator with a manual defrost freezer for a quality performance with energy savings
Door storage	3 full racks offer convenient storage for condiments and bottles
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Fruit and vegetable crisper	Get the longest life and best taste out of produce by storing greens in a convenient slide drawer
Reversible doors	User-reversible door swing for added flexibility
Interior light	Automatically illuminates when you open the door
Removable freezer shelf	Wire shelf provided for flexible storage
Sealed back	Space-saving design that offers easier cleanability

GIDICP962 Specifications:

Overview	
Height of Cabinet	56.0" (142 cm)
Height to Hinge Cap	56.63" (144 cm)
Width	21.5" (55 cm)
Width with Door Open	22.25" (57 cm)
Depth	21.75" (55 cm)
Depth with door at 90°	41.5" (105 cm)
Capacity	7.1 cu.ft. (201 L)
Defrost Type	Cycle
Door	White
Cabinet	White
US Electrical Safety	CSA
Canadian Electrical Safety	CSA-C
Energy Usage/Year	375.0kWh/year
Amps	0.54
Voltage/Frequency	115 V AC/60 Hz
Weight	97.0 lbs. (44 kg)
Shipping Weight	97.0 lbs. (44 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Interior Light	Yes
Refrigerator - Interior Height	36.5" (93 cm)
Refrigerator - Interior Width	17.5" (44 cm)
Refrigerator - Interior Depth	17.0" (43 cm)
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	10.38" (26 cm)

Freezer - Interior Width	15.5" (39 cm)
Freezer - Interior Depth	16.0" (41 cm)
Freezer - Shelf Type	Wire
Freezer - Shelf Qty	1
Thermostat Type	Dial
Refrigerant Type	R600a
Refrigerant Amount	1.62 oz.
High Side PSI	245.0
Low Side PSI	110.0
Level Legs	2

