

# HSM Classic 125.2 High Security

## Powerful and mobile paper shredder

Designed for reliable data destruction in the office



- Meets DOD & NSA/CSS 02-01 mandatory security requirements
- Made for office use up to 5 users
- High quality materials and "Made in Germany" quality for security and durability
- Cutting rollers made of hardened steel with lifetime warranty
- Powerful motor ensures a high cutting capacity and reliable continuous operation
- Paper feed with overload protection reduces paper jams and sustains the high throughput of paper
- The safety element prevents unintentional entry of materials into the machine, increasing user safety
- Easy operation, starts automatically when fed paper and automatically stops after shredding is complete
- Mobile on castors
- High quality wooden cabinet door
- Automatic external oiler ensures long time cutting performance and quality
- Uses a 34 gallon capacity shred bag; Part #HSM3310000004



HSM Part#	HSM15621730
Cutting type	Cross cut
Cutting size	1/32" x 3/16"
Security level DIN 32757-1	6
Security level ISO/IEC 21964	P-7   F-3
Cutting capacity per run in sheets	5 - 7*
Throat opening	10.5"
Motor power (horsepower)	0.9 hp
Voltage	115 V / 60Hz
Dimensions (H x W x D)	29" x 23.2" x 19.2"
Weight	101.41 lbs
Shred-bin volume	24.7 gal
Cutting capabilities	

All technical specifications are approximate values. Technical and design modifications reserved.

\*Sheet capacity will vary depending on paper size, weight, quality and proper power supply.