

HSM Classic 390.3 High Security

Powerful and mobile paper shredder

Designed for open-plan offices



- Meets DOD & NSA/CSS 02-01 mandatory security requirements
- Made for office use by 5 to 8 users
- High quality materials and "Made in Germany" quality for security and durability
- Cutting rollers made of hardened steel with lifetime warranty
- Powerful motor ensures a high cutting capacity and reliable continuous operation
- Paper feed with overload protection reduces paper jams and sustains the high throughput of paper
- The safety element prevents unintentional entry of materials into the machine, increasing user safety
- Easy operation, starts automatically when fed paper and automatically stops after shredding is complete
- Mobile on castors
- High quality wooden cabinet door
- Automatic external oiler ensures long time cutting performance and quality
- Uses a 58 gallon capacity shred bag; Part #HSM331000015



HSM Part#	HSM16601430
Cutting type	Cross cut
Cutting size	1/32" x 3/16"
Security level DIN 32757-1	6
Security level ISO/IEC 21964	P-7 F-3
Cutting capacity per run in sheets	10 - 12*
Throat opening	16"
Motor power (horsepower)	1.9 hp
Voltage	115 V / 60Hz
Dimensions (H x W x D)	35" x 26.4" x 19.2"
Weight	125.6 lbs
Shred-bin volume	38.3 gal
Cutting capabilities	

All technical specifications are approximate values. Technical and design modifications reserved.
 *Sheet capacity will vary depending on paper size, weight, quality and proper power supply.