

Product Name:	PF051WWW/0M30
Description:	<p>Corepoint Scientific™ White Diamond Series Undercounter Freezer Freestanding (-30°C) 4 Cu. Ft. Capacity</p> <p>One solid swing door, right hinged, not reversible</p> <p>Microprocessor temperature controller</p> <p>Digital temperature display</p> <p>Audible and visual high and low temperature alarms</p> <p>2 probes; 1 in air and 1 in sample bottle</p> <p>Remote alarm contacts</p> <p>Adjustable operating temperature range: -27°C – -33°C</p> <p>Three adjustable shelves with guard rail on back to prevent product from being pushed against the back wall</p> <p>Bottom footed shelf to allow air circulation</p> <p>Back wall evaporator cover</p> <p>Keyed door lock</p> <p>Magnetic door gasket for positive seal</p> <p>Recessed door handle</p> <p>Leveling legs</p> <p>LED interior light</p> <p>Probe access port (3/8")</p> <p>White cabinet and door</p> <p>High density urethane foam cabinet and door insulation</p> <p>HFC-free refrigerant (R290), foam insulation and packaging</p> <p>Three year parts and labor warranty, plus an additional two year compressor parts only warranty</p> <p>Exterior dimensions: 23 3/4" W x 24"D x 32 1/8"H</p> <p><i>Note: This unit must have 4" clearance on sides and back for adequate ventilation</i></p> <p>Manual defrost</p> <p>115V, 60 Hz, 2.2 Amps, 1/4 HP</p> <p>UL/C-UL listed</p> <p>Shipping weight: 128 lbs.</p>