FF051WWW/0M
Corepoint Scientific™ White Diamond Series Undercounter Flammable Storage Freezer Freestanding 4 Cu. Ft. capacity  One solid swing door, right hinged, not reversible Microprocessor temperature controller Digital temperature display  Audible and visual high and low temperature alarms 2 probes; 1 in air and 1 in sample bottle  Remote alarm contacts  Adjustable operating temperature range: -15°-25°C  2 fixed shelves with three removable baskets  Keyed door lock  Magnetic door gasket for positive seal Integrated door handle  One probe access port (3/8")  White cabinet and door  High density urethane foam cabinet and door insulation  HFC-free refrigerant (R600a), foam insulation and packaging  Three year parts and labor warranty, plus an additional two year compressor parts only warranty  Note: This unit must have 4" clearance on sides and back for adequate ventilation  Exterior dimensions: 23 5/8"W x 24 1/4"D x 32 3/16" H  Manual defrost  115V, 60 Hz, 1.4 Amps, 1/8 HP  UL/C-UL listed  Units meet NFPA guidelines 45 and 70  Shipping weight: 118 lbs.