

Product Name:	PF051WWWADA/0M
Description:	<p>Corepoint Scientific™ White Diamond Series Undercounter Freezer Built-In 4.2 Cu. Ft. Capacity One solid swing door, right hinged* Microprocessor temperature controller Digital temperature display Audible and visual high and low temperature alarms 2 probes; 1 in air and 1 in sample bottle Remote alarm contacts Adjustable operating temperature range: -15°C – -25°C Two fixed shelves Keyed door lock Magnetic door gasket for positive seal Recessed door handle Leveling legs Probe access port (3/8") Powder coat exterior High density urethane foam cabinet and door insulation HFC-free refrigerant (R600a), foam insulation and packaging Three year parts and labor warranty, plus an additional two year compressor parts only warranty Pyxis®, Omnicell® and AcuDose RX® compatible Exterior dimensions: 23 ¾ "W x 24 ½ "D x 31 15/16 "H Manual defrost 115V, 60 Hz, 1.5 Amps, 1/8 HP ADA compliant UL/C-UL listed Shipping weight: 133 lbs. *This product is available left hinged, product number PF051WWWADALH/0M</p>