

Product Name:	NSWDUF171JWJ/0
Description:	<p>Corepoint Scientific™ White Diamond Series Ultra Low Temperature Freezer 17 Cu.Ft. Capacity</p> <p>One solid swing exterior door, right hinged, not reversible</p> <p>Five insulated inner doors</p> <p>Microprocessor controller specifications</p> <p>Touch pad keys and four line display for easy programming</p> <p>Large LED temperature readout</p> <p>Audible and visual alarms with silence key for audible alarms Programmable high and low temperature alarm set points</p> <p>Programmable access code to limit access to set points and controller configuration</p> <p>Automatic voltage boost to compensate for low line voltages</p> <p>Normally open, normally closed alarm contacts and 4-20mA signal available to connect to central alarm system</p> <p>RS-232 serial output</p> <p>Battery backup on electronics during power outages</p> <p>Temperature range: -50°C to -86°C</p> <p>Four stainless steel shelves, adjustable on ½" centers</p> <p>Cam action handle for one hand latching of exterior door.</p> <p>Handle supplied with key lock and door switch for audible and visual alarms</p> <p>Four heavy duty swivel casters with locks</p> <p>Vacuum relief port for quick access after door closures</p> <p>CFC-free refrigerant</p> <p>Two year parts and labor warranty, plus an additional three year compressor parts warranty</p> <p>Exterior dimensions: 37.6"W x 36.3"D x 79.6"H</p> <p>Interior dimensions: 23.4"W x 23"D x 50"H</p> <p>2" box capacity: 320 ea.</p> <p>Upright freezer rack capacity: 20 ea. UF442 racks</p> <p>115V, 60Hz, 16 amp, HP: ½ x ½</p> <p>UL/C-UL Listed</p> <p>NEMA plug configuration: NEMA 5-20</p> <p>Cascade refrigeration system</p> <p>Shipping weight: 700 lbs.</p>