

Product Name:	PRF122WWG/0
Description:	<p>Corepoint Scientific™ White Diamond Series Refrigerator &amp; Freezer Combination  12 Cu. Ft. capacity (10.5 Ref./1.7 Freezer)  Two exterior swing doors (glass door refrigerator/solid door freezer), right hinged, not reversible  Microprocessor temperature controller, refrigerator and freezer  Digital temperature display with sample simulated probe, refrigerator and freezer  Adjustable operating temperature range: Refrigerator: 1°C – 10°C; Freezer: -15°C – -25°C  Audible and visual high and low temperature alarms, refrigerator and freezer  Remote alarm contacts, refrigerator and freezer  Six adjustable shelves with guard rail on back to prevent product from being pushed against back wall, Refrigerator  Two adjustable shelves with guard rail on back to prevent product from being pushed against back wall, Freezer  Bottom footed shelf to allow air circulation, Refrigerator and Freezer  Forced draft circulation Refrigerator  Keyed door locks  Magnetic door gasket for positive seal  Integrated door handles  Leveling legs  Stacking kit  LED interior lights  Two probe access ports (3/8"); one, refrigerator/one, freezer  White powder coated exterior  HFC-free refrigerant (R600a), foam insulation and packaging Three year parts and labor warranty, plus an additional two year compressor parts warranty  Exterior dimensions: 23 5/8" W x 26 1/2" D x 80 1/4" H  Manual defrost freezer / cycle defrost refrigerator  115V, 60 Hz, 2.3 Amps refrigerator, 1 Amp freezer, 1/3 HP refrigerator, 1/8 HP freezer  UL/C-UL listed  Shipping weight: 316 lbs.  <b>In stock, with next day shipping</b>  *Please note this unit requires 2 outlets.</p>