Product Name:	PRF092WWG/0
Description:	PRF092WWG/0 Corepoint Scientific™ White Diamond Series Refrigerator & Freezer Combination 9 Cu. Ft. Capacity (4.6 Ref./4.2 Freezer) Two exterior swing doors (glass door refrigerator/solid door freezer), right hinged* Microprocessor temperature controller, refrigerator and freezer Digital temperature display with sample simulated probe, refrigerator and freezer Audible and visual high and low temperature alarms, refrigerator and freezer Remote alarm contacts, refrigerator and freezer Adjustable operating temperature range: Refrigerator: 1°C − 10°C; Freezer: -15°C25°C 2 adjustable/1 fixed shelves refrigerator with guard rail on back to prevent product from being pushed against back wall/2 fixed shelves freezer Keyed door locks Magnetic door gasket for positive seal Recessed door handle, freezer; heavy duty door handle, refrigerator Leveling legs Stacking kit LED interior light, Refrigerator Two probe access ports (3/8"); one, refrigerator/one, freezer White powder coated exterior High density urethane foam cabinet and door insulation HFC-free refrigerant (R600a), foam insulation and packaging Exterior dimensions: 23 ¾" W x 25 ½"D x 66 ¾"H Three year parts and labor warranty, plus an additional two year compressor parts warranty Manual defrost freezer / cycle defrost refrigerator 115V, 60 Hz, 1.74 Amps Refrigerator, 1.5 Amps Freezer, 1/8 HP Refrigerator and Freezer UL/C-UL listed Shipping weight: 282 lbs.
	*This product is available left hinged, product number PRF092WWGLH/0