

Product Name:	PRF092SSSLH/0
Description:	<p>Corepoint Scientific™ White Diamond Series Refrigerator & Freezer Combination-LEFT HINGED 9 Cu. Ft. Capacity (4.5 Ref./4.2 Freezer) Two stainless steel exterior swing doors, left hinged, not reversible Microprocessor temperature controller, refrigerator and freezer Digital temperature display with sample simulated probe, refrigerator and freezer Adjustable operating temperature range: Refrigerator: 1°C – 10°C; Freezer:-15°C – -25°C Audible and visual high and low temperature alarms, refrigerator and freezer Remote alarm contacts, refrigerator and freezer 2 adjustable/1 fixed shelves refrigerator/2 fixed shelves freezer with guard rails on back in Refrigerator to prevent product from being pushed against back wall Back wall evaporator cover, Refrigerator Forced draft circulation Refrigerator Keyed door locks Magnetic door gasket for positive seal Recessed door handles Leveling legs Stacking kit LED interior lights Probe access port (3/8"), 2 ea. (1 for refrigerator/1 for freezer) Stainless steel exterior HFC-free refrigerant (R600a), foam insulation and packaging Three year parts and labor warranty, plus an additional two year compressor parts warranty Exterior dimensions: 23 ¾" W x 24 ½"D x 66 ¾"H Manual defrost freezer / cycle defrost refrigerator 115V, 60 Hz, 1.74 Amps Refrigerator, 1.5 Amps Freezer, 1/8 HP Refrigerator and Freezer UL/C-UL listed Shipping weight: 266 lbs. *Please note this unit requires 2 outlets.</p>