

Product Name:	GPF231SSS/0A
Description:	<p>Corepoint Scientific™ General Purpose Stainless Steel Freezer 23 Cu. Ft. capacity One swing solid door, self-closing, right hinged, not reversible 3 ea. Adjustable Shelves Digital display microprocessor temperature controller Adjustable operating temperature: 5°F – -13°F (-15°C - -25°C) Audible and visual Hi/Lo temperature alarm 2 probes; 1 in air and 1 in sample bottle Probe attached to evaporator for defrost termination sensing Sensor error alarm Continuous product (simulated) temperature display Remote alarm contacts Forced draft air circulation Keyed door lock Magnetic door gaskets for positive seal Integrated door handle LED interior lights are safety shielded and switch controlled Probe access port (3/4") Stainless steel exterior White-powder coated aluminum interior with 304 stainless steel floor Easily cleaned smooth interior Hydrocarbon natural refrigerant (R290) 2 year parts and labor warranty, plus an additional 3 year compressor parts warranty Auto defrost 4 swivel casters (5 3/4") Exterior dimensions: 26 7/8" W x 33 3/4" D x 83 1/4" H with casters; 77 1/2" H without casters 115V, 60 Hz, 8 Amps, 3/4 HP ETL listed Shipping weight: 327 lbs.</p>