	NODICE (INONIE)
Product Name:	NSRI231WSW/0
Description:	
	23 Cu. Ft. Capacity
	One swing solid door, self-closing, right hinged, not reversible
	Three, 304 stainless steel sliding tray shelves
	Controller Information:
	Proportional integral derivative (PID) controller with graphic display
	Programmable ramp and soak
	Process phase graphic animations
	USB data port
	RS-485 communication (MODBUS-RTU)
	Real time clock
	Battery backup
	Event logs: 100
	Visual alarm indicator
	Audible alarm indicator
	Process phase specific temp alarm
	Power failure alarm
	Sensor failure alarm
	• Sensor failure alarm Temperature setpoint range: 4°C to 70°C Temperature control: +/- 0.1°C Temperature stability: +/- 0.5°C from 4°C to 70°C (Range dependent per test protocol) Temperature uniformity: +/- 1°C from 4°C to 70°C (Range dependent per test protocol) Cabinet is foamed-in-place with EPA compliant high density; polyurethane foam insulation White-powder coated steel exterior 304 stainless steel interior Plenum air distribution Top mounted, variable speed compressor Hydrocarbon natural refrigerant Multi-element, independent proportional electric heating Temp sensor Type: NTC Condensate evaporation Shielded, switched interior LED lighting Heavy duty door handle Magnetic door gasket for positive seal Keyed door lock Probe access port (3/4") 4 swivel casters (3 1/2") 18 months parts and labor warranty 5 year compressor warranty

Exterior dimensions: 26 7/8" W x 36 3/8" D x 81 1/2" H with casters;
77 1/4" H without casters
Interior dimensions: 22" W x 25 1/2" D x 59" H
115V, 60 Hz, 12 Amps, 1/3 HP
ETL Listed
Shipping weight: 380 lbs.