

Telephone: (845) 365-8200 * Website: www.dynarex.com
Toll Free: (888) DYNAREX * Website: www.thcnet.com
Fax: (845) 365-8201

Reorder # 1108, 1201-1202-1207; HS-1125637

Reviewed on 1/7/15

Safety Data Sheet

SECTION 1. Product and Company Identification

Product/Trade Name: Povidone iodine pads
Povidone iodine swabsticks

Manufacturer's Name: Dynarex Corporation

Manufacturer's Address: 10 Glenshaw Street
Orangeburg, NY 10962

Emergency or Information Phone No.: 888-DYNAREX or 845-365-8201
At other times, contact the local Poison Control Center

SECTION 2. Hazards Identification

Flash Point: >200°F (>90°C)

Hazardous Decomposition of Byproducts: Emits iodine vapors at high temperatures

Hazard Rating (NFPA): Health: 1
Flammability: 1
Reactivity: 0
Specific: None

SECTION 3. Composition/Information on Ingredients

INGREDIENTS	CAS NUMBER	WT. %	ACGIH-TLV
Povidone Iodine Complex	2565-5418	0.5 to 3	None Established

SECTION 4. First-Aid Measures

Skin Contact: Discontinue if rash or irritation is noted.

Eye Contact: Flush with cool water for 15 minutes.

Inhalation: None

Ingestion: Do not induce vomiting. Get medical attention.

Telephone: (845) 365-8200 * **Website:** www.dynarex.com
Toll Free: (888) DYNAREX * **Website:** www.thcnet.com
Fax: (845) 365-8201

Target Organs: N/A

SECTION 5. Fire-Fighting Measures

Extinguishing Media: Any
Special Fire-fighting Procedures: None
Unusual Fire and Explosion Hazards: May emit toxic fumes of iodine in a fire.

SECTION 6. Accidental Release Measures

Use absorbent material and dispose per local regulations.

SECTION 7. Handling and Storage

Avoid storing at extreme temperatures.

Store under dry conditions.

SECTION 8. Exposure Controls/Personal Protection

Respiration: None
Ventilation: None
Protective Gloves: If handling liquid
Eye Protection: If splashing is a hazard
Hygienic Practices: Good housekeeping practices should be followed.
Other: Wear apron to protect clothing.

SECTION 9. Physical and Chemical Properties

Color/Appearance: Applicator saturated with dark reddish brown liquid
Odor: Faint Iodine
Boiling Point: N/A
Vapor Density: N/A
Evaporation Rate: N/A
Solubility in Water: Soluble
Specific Gravity (H₂O=1): N/A

SECTION 10. Stability and Reactivity

Stability:	Stable
Conditions to avoid:	None known
Incompatibility:	Alkalis and reducing agents
Hazardous Decomposition of By-products:	Emits iodine vapors at high temperatures
Polymerization:	Will not occur

SECTION 11. Toxicological Information

Skin:	May cause irritation
Eyes:	May be irritating
Inhalation:	None
Ingestion:	Harmful

SECTION 12. Ecological Information

Ecotoxicity Not available
Environmental effects Not available
Aquatic toxicity Not available
Persistence / degradability Not available
Bioaccumulation / accumulation Not available
Partition coefficient Not available
Mobility in environmental media Not available
Chemical fate information Not available
Other adverse effects Not available

SECTION 13. Disposal Considerations

Follow local, state and federal regulations.

SECTION 14. Transport Information

DOT Shipping Name:
Technical Shipping Name:

Telephone: (845) 365-8200 * **Website:** www.dynarex.com
Toll Free: (888) DYNAREX * **Website:** www.thcnet.com
Fax: (845) 365-8201

DOT Shipping Classification: **DOT not regulated**

DOT ID Number:

DOT Label Requirements:

UN/NA Number Regulations:

Reportable Quantity:

SECTION 15. Regulatory Information

Canadian federal regulations This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the MSDS contains all the information required by the Controlled Products Regulations.

NPN 00489948 - Pad/ NPN 00489964 - Swabstick

US Federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200 due to the presence of listed sensitizers. All components are on the U.S. EPA TSCA Inventory List.

Occupational Safety and Health Administration (OSHA)

29 CFR 1910.1200 hazardous chemical Yes

CERCLA (Superfund) reportable quantity

Sodium hydroxide: 1000.0000

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

Immediate Hazard - Yes
Delayed Hazard - Yes
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

Section 302 extremely hazardous substance

No

Section 311 hazardous chemical Yes

Clean Air Act (CAA) Not available

Clean Water Act (CWA) Not available

Safe Drinking Water Act (SDWA) Not available

Drug Enforcement Agency (DEA) Not available

Food and Drug Administration (FDA) Not available

WHMIS classification Exempt - Registered product - (NHP see above)

State regulations This product does not contain a chemical known to the State of California to cause cancer, birth defects or other reproductive harm.

Telephone: (845) 365-8200 * **Website:** www.dynarex.com
Toll Free: (888) DYNAREX * **Website:** www.thcnet.com
Fax: (845) 365-8201

SECTION 16. Other information

Abbreviations

N/A: Denotes no applicable information found or available
CAS#: Chemical Abstracts Service Number
ACGIH: American Conference of Governmental Industrial Hygienists
OSHA: Occupational Safety and Health Administration
TLV: Threshold Limit Value
PEL: Permissible Exposure Limit
STEL: Short Term Exposure Limit
NTP: National Toxicology Program
IARC: International Agency for Research on Cancer
EU: European Union
R: Risk
S: Safety

Disclaimer: This Safety Data Sheet, which takes into consideration the requirements of Directive 76/768/EC and subsequent amendments and Directive 1999/45/EC plus subsequent amendments, has been prepared in accordance with Directive (EC) 1907/2006. It is believed to be correct and corresponds to the latest scientific/technical knowledge but all data, instructions, recommendations and/or suggestions are made without guarantee. No warranty, expressed or implied, is made and Dynarex Corp. assumes no legal responsibility or liability resulting from its use.

This document was created with Win2PDF available at <http://www.win2pdf.com>.
The unregistered version of Win2PDF is for evaluation or non-commercial use only.
This page will not be added after purchasing Win2PDF.