



Ultra-IBC Hard Top Steel Model

Product Data Sheet

| | |
|----------------------------------|---|
| Part# | 1185 |
| Description | Steel IBC Hard Top |
| Outer Dimensions in. (mm) | 71.2 x 66.4 x 83.3 (1808.5 x 1686.6 x 2115.8) |
| Internal Dimensions in. (mm) | 64.9 x 60.1 x 53.8 (1648.5 x 1526.5 x 1366.5) |
| Door Opening Dimensions in. (mm) | 52 L x 49.8 H (1321 L x 1264.9 H) |
| Load Capacity UDL lb.(kg) | 5,640 (2,558) |
| Sump Capacity gal. (L) | 370 (1400) |
| Weight lb. (kg) | 660 (299) |
| Composition | Steel (14 gauge painted sump, 16 gauge galvanized top) |
| Color | Yellow / Silver |
| Capacity | One (1) IBC tank or tote |
| Compliance | Meets SPCC and EPA Container Storage Regulation 40 CFR 264.175 Spill Containment Regulations. |

FOB: Quebec, Canada

