



SP-900SD

1.5" SUBMERSIBLE PUMP



SPECIFICATIONS

1.5" SIDE DISCHARGE W/ FLOAT

1 HP, 115V, 1100W
TETHERED FLOAT SWITCH
4360 GAL /HR CAPACITY
31 FT MAX DELIVERY HEIGHT
23 FT MAX SUBMERSIBLE DEPTH
0.2" MAXIMUM SOLID HANDLING
COPPER WINDINGS
MECHANICAL SEAL
25 FT CORD
STAINLESS STEEL/PLASTIC BODY

PART# SP-900SD

PUMP
WARRANTY

