



SP-750TD

1.5" SUBMERSIBLE PUMP



SPECIFICATIONS

1.5" TOP DISCHARGE W/ FLOAT

3/4 HP, 115V, 750W
TETHERED FLOAT SWITCH
2905 GAL /HR CAPACITY
28 FT MAX DELIVERY HEIGHT
26 FT MAX SUBMERSIBLE DEPTH
0.2" MAXIMUM SOLID HANDLING
COPPER WINDINGS
MECHANICAL SEAL
25 FT CORD
STAINLESS STEEL BODY

PART# SP-750TD

PUMP
WARRANTY

