

The right way to choose the right earmuff.

3M™ Peltor™ Optime™ Earmuffs

The **3M Peltor Optime 95** earmuffs feature a lightweight, low-profile design that helps improve comfort and fit. Four different headband options make it possible to use Optime 95 earmuffs in a wide variety of situations. Recommended for eight-hour TWA noise exposures up to 95 dBA.



Optime 95 - H6A/V Earmuff - standard headband**

NRR 21 dB†

Optime 95 - H6B/V Earmuff - neckband

NRR 21 dB†

Optime 95 - H6P3E/V Earmuff - hard hat-attached version

NRR 21 dB†

Optime 95 - H6F/V Earmuff - folding headband

NRR 21 dB†

PRODUCT NUMBER	UPC NUMBER	ABBREVIATED GENERAL DESCRIPTION	CASE QUANTITY
H6A/V	10093045080615	Low Profile Over-the-Head Beige Earmuff NRR 21 dB*	10
H6B/V	10093045080622	Low Profile Behind-the-Head Beige Earmuff NRR 21 dB*	10
H6F/V	10093045080639	Low Profile Folding Beige Earmuff NRR 21 dB*	10
H6P3E/V	10093045080653	Low Profile Hard Hat-Attached Beige Earmuff NRR 21 dB*	10
HY3	07318640051614	Replacement Hygiene Kit 1 Pr Cushions/1 Pr Foam Inserts for H6, H9 and H31 Type Hearing Protectors	20

The **3M Peltor Optime 98** earmuffs are some of the most versatile earmuffs in the industry today. Recommended for eight-hour TWA noise exposures up to 98 dBA.



Optime 98 - H9A Earmuff - standard headband**

NRR 25 dB†

Optime 98 - H9P3E Earmuff - hard hat-attached version

NRR 23 dB†

PRODUCT NUMBER	UPC NUMBER	ABBREVIATED GENERAL DESCRIPTION	CASE QUANTITY
H9A	10093045080912	Over-the-Head Yellow Earmuff NRR 25 dB*	10
H9P3E	10093045080936	Hard Hat-Attached Yellow Earmuff NRR 23 dB*	10
HY3	07318640051614	Replacement Hygiene Kit 1 Pr Cushions/1 Pr Foam Inserts for H6, H9 and H31 Type Hearing Protectors	20

3M Peltor Optime 101 earmuffs are recommended for eight-hour TWA noise exposures up to 101 dBA. With three different headband options, there is an Optime 101 earmuff for a wide range of industrial applications.



Optime 101 - H7A Earmuff - standard headband**

NRR 27 dB[†]

Optime 101 - H7B Earmuff - neckband

NRR 26 dB[†]

Optime 101 - H7P3E Earmuff - hard hat-attached version

NRR 24 dB[†]

PRODUCT NUMBER	UPC NUMBER	ABBREVIATED GENERAL DESCRIPTION	CASE QUANTITY
H7A	10093045080714	Over-the-Head Green Earmuff NRR 27 dB*	10
H7B	10093045080721	Behind-the-Head Green Earmuff NRR 26 dB**	10
H7P3E	10093045080738	Hard Hat-Attached Green Earmuff NRR 24 dB*	10
H7P3E-01	07318640051652	Hard Hat Attached Electrically Insulated (Dielectric) Green Earmuff NRR 24 dB*	10
HY7	10093045087706	Replacement Hygiene Kit for H7 Type Hearing Protectors	20

3M Peltor Optime 105 earmuffs are recommended for high-noise exposure situations; eight-hour TWA noise exposures up to 105 dBA. The Optime 105 earmuffs feature a “double-shell” cup design that helps improve attenuation across the entire range of frequencies.



Optime 105 - H10A Earmuff - standard headband**

NRR 30 dB[†]

Optime 105 - H10B Earmuff - neckband

NRR 29 dB[†]

Optime 105 - H10P3E Earmuff - hard hat-attached version

NRR 27 dB[†]

PRODUCT NUMBER	UPC NUMBER	ABBREVIATED GENERAL DESCRIPTION	CASE QUANTITY
H10A	10093045081018	Over-the-Head Green Earmuff NRR 30 dB*	10
H10A HV	10093045981721	Hi-Viz Over-the-Head Green Earmuff NRR 30 dB*	10
H10B	10093045081025	Behind-the-Head Dual Cup Earmuff NRR 29 dB*	10
H10P3E	10093045081032	Hard Hat-Attached Dual Cup Earmuff NRR 27 dB*	10
H10P3E-01	10093045978301	Hard Hat Attached Dual Cup Electrically Insulated (Dielectric) Earmuff NRR 27 dB*	10
HY10	10093045081049	Hygiene Kit 1 Pr Cushions/1 Pr Foam Inserts for H10 Series	20