
## DELUXE ROLLER STAND, STAND-H



## STANDARD FEATURES

MODEL NUMBER: STAND-H CAPACITY: 1760 LBS

LOWERED HEIGHT(MIN): 24 7/16"
RAISED HEIGHT(MAX): 39 1/2"
14" HORIZONTAL ROLLER
HEAVY-DUTY CAST-ST'L BASE

ADJUSTABLE HEIGHT

ROLLER IS 2" DIA & CHROME PLATED

## SPECIAL FEATURES

NONE

\*\*Any additions, deletions or omissions must be corrected on this drawing, as this drawing will be considered all inclusive.\*\*

\*\*SPECIAL UNITS ARE NON-RETURNABLE
\*AVAILABLE AT ADDITIONAL COSTS

\*\*\* ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY.

IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY
THOSE DIMENSIONS WITH YOUR SALESPERSON. \*\*\*

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

## APPROVAL

I, the undersigned, hereby approve this print

[] As drawn
[] As marked
This includes my approval of design & dimensions.
Signed:
Date:

DISTRIBUTOR'S NAME:		P. 🛮 . # : 🔝
VESTIL	MANUFACTURING	₩.□.#: _
DRÁWN BY: 🔲W	<sup>DATE</sup> : 7-31-06	SALES: –
REFERENCE:		DRWG.∕FILE NAME:
_	SC/LE: 1.12	H-UN/12