
HEAVY DUTY MANUAL TURNTABLE- TT-30-7/8 APPROX WEIGHT: 66.81 lbs.

ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE

NOTE: GROOVES IN TURNTABLE NOT SHOWN FOR CLARITY



FOR INTERNAL USE ONLY PROJECT SIGN OFF **SALES** ENG. FAB. **POWER DIMENSION TOLERANCE ± 1/4"**

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

STANDARD FEATURES

MODEL NUMBER: TT-30-7/8 UNIFORM CAPACITY: ,1000 LBS. TURNTABLE DIAMETER: Ø30" **OVERALL HEIGHT: 13/16"**

5/16" TOP PLATE

RUBBER COVER ON TOP PLATE

SPECIAL FEATURES

NONE

DIVIDITY TOLD IN THE
I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS
REPRESENTED SATISFIES DESIGN AND DIMENSION
DECLUDE A FRITCH A LCC A CICKLOVALLED CE A AVIDUTY TO

REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE

AND LOCAL REGULATIONS AND STANDARDS. ANY MODIFIED UNITS ARE NON-RETURNABLE

	[] As drawn	[] As marked	
Signed:		Date:	

P

P

R

0

V

Α

1	Printed Name:		
	LEAD TIME WILL START UP	ON RECEIPT OF SIGNED	APPROVAL DRAWING
D	DISTRIBUTOR'S NAME:	P.O.# X	
	VESTIL MANUFAC	W.O.# v	
Г	DPAWNIRY	CALES	
_	DRAWN BY: ADL	DATE: 08/01/05	SALES: X
R	EFERENCE: X	SCALE: 1:8	FILE NAME:
G	QUOTED LEAD TIME: X	QUOTE # '	20-007-053