
## HEAVY DUTY PRECISION TURRET BEARING - PTB-19 APPROX WEIGHT: 98 LBS DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\*ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE\*\*\*




P

P

R

O

٧ Α





FOR INTERNAL USE ONLY PROJECT SIGN OFF **SALES** ENG. FAB. **POWER** 

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

## STANDARD FEATURES

MODEL# PTB-19 **DIAMETER: 19 1/8"** HEIGHT: 2 1/4" CAPACITY: 6000 LBS LOW PROFILE DESIGN

SUPERIOR PLATED FINISH FOR CORROSION RESISTANCE

GREASE-ABLE POINTS FOR SIMPLE MAINTENANCE

SHIELDED BEARINGS TO PROTECT DEBRIS AND **RETAIN GREASE** 

MULTIPLE BOLT LOCATIONS FOR MOUNTING

CAPTURED BALL BEARING DESIGN PREVENTS RINGS FROM SEPARATING

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.

## ANY MODIFIED UNITS ARE NON-RETURNABLE

[ ] As marked

[ ] As drawn

	[ ]	[ ]	
Signed:		Date:	
•			

Printed Name:

LEAD TIME WILL START UPO	ON RECEIPT OF SIGNED	APPROVAL DRAWING
DISTRIBUTOR'S NAME:	P.O.# X	
VESTIL MANUFAC	W.O.# X	
DRAWN BY: X	DATE: XX/XX/XX	SALES: X
reference: X		FILE NAME:
DUOTED LEAD TIME: X	QUOTE #	PTB-19