
HINGE TILT TABLE - EHTT

APPROX WEIGHT: 657,6956 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER: EHTT

CAPACITY: 4,000 LBS. EVENLY DISTRIBUTED

PLATFORM WIDTH: 48"

PLATFORM LENGTH: 47 3/4"

LEVEL HEIGHT: 10"

LIP HEIGHT: 12"

MAXIMUM TILT ANGLE: 45°

DOUBLE ACTING HYDRAULIC CYLINDER

W/ DOWN VELOCITY FUSE

INTERNAL POWER UNIT

24 V HAND CONTROL ON 8 FT. COIL CORD UPPER & LOWER TILT LIMIT SWITCHES

DURABLE LIQUID PAINT BLUE FINISH

4- Ø5/8" MOUNTING HOLES

PLEASE CIRCLE SPECIFICATIONS: **POWER**

MOTOR VOLTAGE 115 208 DEDICATED CIRCUIT REQUIRED 60Hz

MOTOR PHASE **THREE**

CONTROL **HAND**

SPECIAL FEATURES

SALES

ENG.

FAB.

POWER

NONE

FOR INTERNAL USE ONLY

PROJECT SIGN OFF

V

Α

NOTE: EHTT MUST BE ANCHORED TO FLOOR

DIMENSION TOLERANCE ± 1/4"

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION Α REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION Ρ COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE Ρ AND LOCAL REGULATIONS AND STANDARDS. R 0

ANY MODIFIED UNITS ARE NON-RETURNABLE

[] As drawn 1 As marked Signed: Date:

Printed Name:

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:

VESTIL MANUFACTURING W.O.# DRAWN BY: CRA SALES: X 03/20/2019 reference: X SCALE: 1:20 FILE NAME:

Χ

QUOTED LEAD TIME: X QUOTE # 38-007-005