

APPROX WEIGHT: 358.86 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGE

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON





Ρ

Ρ

0

STANDARD FEATURES

MODEL NUMBER: COL-4-36-33 OVERALL SIZE:

29 1/4" W x 91" L x 82 7/8" H CLEARANCE SPAN:

38 1/8" W x 38 1/4" H TOP PLATFORM HEIGHT: 40" STEP HEIGHT SPACING: 10"

STEP DEPTH: 7"

STEP & PLATFORM WIDTH 23 1/2"

CLIMB ANGLE: 58°

ALL STEPS & PLATFORM ARE SERRATED STEEL KNOCK-DOWN HANDRAILING (UNIT SHIPS KNOCKED DOWN, ASSEMBLY REQUIRED)

SPECIAL FEATURES NONE

NOTE

UNIT MUST BE ANCHORED TO
THE FLOOR!!!
Ø7/16" MOUNTING HOLES
8 TOTAL MOUNTING HOLES PER
STANDARD UNIT
2 MOUNTING HOLES PER CORNER
BRACKET

LI	ES PEF	R CORNER				
	FOR INTE	INTERNAL USE ONLY DIS				
	SALES		DB			
	ENG.					
	FAB.		REI			
	POWER		Ql			

DIMENSION TOLERANCE I 1/4
I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS
REPRESENTED SATISFIES DESIGN AND DIMENSION
REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO
CONFIRM PRODUCT AND INSTALLATION
COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE
AND LOCAL REGULATIONS AND STANDARDS.
ANY MODIFIED UNITS ARE NON-RETURNABLE

ANY MODIFIED UNITS ARE NON-RETURNABLE

[] As drawn [] As marked

Signed:_____Date:____

	LLAD TIME WILL START OF OF	VINLULII I OI SIONED AIT NOVAL DINAVIIN
7	DISTRIBUTOR'S NAME:	P.O.# X

DISTRIBUTOR'S NAME:			P.O.# X
VESTIL MANUFAC	W.O.# X		
	DATE: 4/2		SALES: X
reference: X		SCALE: 1:24	FILE NAME:
QUOTED LEAD TIME: V	QUOTE #		44-007-065

Χ