
CROSS-OVER LADDER - COL-5-46-23

APPROX WEIGHT: 359.68 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER: COL-5-46-23 OVERALL SIZE:

29 1/4" W x 91 1/2" L x 92 7/8" H CLEARANCE SPAN:


26 1/8" W x 48 1/4" H TOP PLATFORM HEIGHT: 50" STEP HEIGHT SPACING: 10"

STEP DEPTH: 7"

STEP & PLATFORM WIDTH 23 1/2"

CLIMB ANGLE: 58°

ALL STEPS & PLATFORM ARE SERRATED STEEL KNOCK-DOWN HANDRAILING (UNIT SHIPS KNOCKED DOWN, ASSEMBLY REQUIRED)



SPECIAL FEATURES NONE

NOTE

UNIT MUST BE ANCHORED TO
THE FLOOR!!!
Ø7/16" MOUNTING HOLES
8 TOTAL MOUNTING HOLES PER
STANDARD UNIT
2 MOUNTING HOLES PER CORNER
BRACKET

L	ES PEF	RCORNER	LEAD TIME WIL	
	FOR INTERNAL USE ONLY PROJECT SIGN OFF		DISTRIBUTOR'S NAME: VESTIL MA	
	SALES		DRAWN BY: BCN	
	ENG.			
	FAB.		reference: X	
	POWER		QUOTED LEAD TIME: χ	

	DIMENSION TOLLIVANCE :
	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS
	REPRESENTED SATISFIES DESIGN AND DIMENSION
Α	REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO
Р	CONFIRM PRODUCT AND INSTALLATION
P	COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE
	AND LOCAL REGULATIONS AND STANDARDS.
R	ANY MODIFIED UNITS ARE NON-RETURNABLE
0	

[] As drawn [] As marked
Signed: Date:

Printed Name:_____

44-007-067

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING
STRIBUTOR'S NAME:

P.O.# ,,

VESTIL MANUFAC	W.O.# X	
DRAWN BY: BCN	4/29/2010	SALES: X
reference: X	SCALE: 1:24	FILE NAME:

QUOTE #