APPROX WEIGHT: 337.10 lbs. ADJUSTABLE IBC TILT STAND W/ FORK POCKETS - IBC-TLT-FPL *** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON 48 34 3/8" 58 3/8' 23 1/4" RAISED 19 1/2" LOWERED SPECIAL FEATURES NONE DIMENSION TOLERANCE ± 1/4" I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. P STANDARD FEATURES Ρ MODEL NUMBER IS: IBC-TLT-FPL R MAX CAPACITY IS: 4,400 LBS UNITS REQUIRING APPROVAL DRAWINGS OR 0 **OVERALL WIDTH IS: 48"** MODIFIED ARE NON-RETURNABLE USABLE WIDTH IS: 40 1/2" [] As drawn [] As marked Α **OVERALL LENGTH IS: 48 1/2"** Signed: **USABLE LENGTH IS: 47 3/4" OVERALL HEIGHT IS: 34 3/8"MIN Printed Name:** 58 3/8" MAX LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING HEIGHT ADJUSTMENT IN: 6" INCREMENTS DISTRIBUTOR'S NAME: FOR INTERNAL USE ONLY PLATFORM HEIGHT IS: 23 1/4" RAISED PROJECT SIGN OFF W.O.# X VESTIL MANUFACTURING 19 1/2" LOWERED **SALES** DATE: 8/4<u>/2020</u> SALES: X 2" X 7" FORK POCKETS ON 27"CENTERS ENG. TOUGH BAKED IN POWDER COAT BLUE FINISH SCALE: 1:20 FILE NAME: FEET MUST BE ANCHORED TO GROUND. FAB. QUOTED LEAD TIME: $_{ m Y}$ QUOTE # 16-007-504 POWER Χ