
LIFT AND TILT SCISSOR TABLE - EHLTT-4848-2-47 APPROX WEIGHT: 1120.91 lbs. Does not include weight of power of the power o

APPROX WEIGHT: 1120.91 lbs.

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS EHLTT-4848-2-47 MAX CAPACITY IS 2.000 LBS PLATFORM WIDTH IS 48" FRAME WIDTH IS 30" **OVERALL LENGTH IS 56"** PLATFORM LENGTH IS 48" PLATFORM RAISED HEIGHT IS 47" PLATFORM LOWERED HEIGHT IS 11"

OVERALL HEIGHT IS 83 7/16" PLATFORM TILTS ON THE END OF THE LEG ASSEMBLY PLATFORM TILTING STYLE IS A SLIDE TILT Ø1/4" x 60" CHAIN AND HOOK (NOT DRAWN TO SCALE) MAXIMUM TILT ANGLE IS 45°

SPECIAL FEATURES

PLEASE CIRCLE SPECIFICATIONS:

POWFR AC MOTOR VOLTAGE 115 208 DEDICATED CIRCUIT REQUIRED 60Hz **MOTOR PHASE THREE** CONTROL HAND FOO:

DIMENSION TOLERANCE ± 1/4" I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION Α REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION Р COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE Ρ AND LOCAL REGULATIONS AND STANDARDS. R 0

ANY MODIFIED UNITS ARE NON-RETURNABLE [] As drawn [] As marked

Signed: Date:

Printed Name:

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

Χ

VESTIL MANUFACTURING			W.O.#
DRAWN BY: BCN	DATE: 2/3	/2017	SALES:

REFERENCE: X FAB. QUOTED LEAD TIME: X

FOR INTERNAL USE ONLY

PROJECT SIGN OFF

SALES

ENG.

POWER

٧

Α

SCALE: 1:25 FILE NAME: QUOTE # 02-007-041-001

NONE