


# ROTARY AIR/HYDRAULIC SCISSOR TABLE, AHLT-4048-3-43



## STANDARD FEATURES:

SCISSOR TABLE MODEL NUMBER IS AHLT-4048-3-43  
 PLATFORM WIDTH IS 40 INCHES  
 PLATFORM LENGTH IS 48 INCHES  
 PLATFORM RAISED HEIGHT IS 43 INCHES  
 PLATFORM LOWERED HEIGHT IS 7 INCHES  
 TABLE CAPACITY (EVENLY DISTRIBUTED LOAD) IS 3,000 LBS.  
 CONNECTION: 1/2" NPT AIR LINE  
 HINGED MAINTENANCE PROPS, PNEUMATIC UPPER TRAVEL LIMIT SWITCH,  
 TOE GUARDS, & INTERNAL BRASS VELOCITY FUSE STANDARD

## PLEASE CIRCLE SPECIFICATIONS:

POWER	<input type="checkbox"/> AC	<input type="checkbox"/> DC (<12V)	<input checked="" type="checkbox"/> AIR/OIL	
MOTOR VOLTAGE	<input type="checkbox"/> 115	<input type="checkbox"/> 200	<input type="checkbox"/> 230	<input type="checkbox"/> 460
DEDICATED CIRCUIT REQUIRED				
MOTOR PHASE	<input type="checkbox"/> SINGLE		<input type="checkbox"/> THREE	
CONTROL	<input checked="" type="checkbox"/> HAND		<input type="checkbox"/> *FOOT	
POWER UNIT LOCATION	<input checked="" type="checkbox"/> INTERNAL		<input type="checkbox"/> *EXTERNAL	

Deck tolerances +/- 1/2"  
 Table height tolerances +/- 1/2"  
 Deck Flatness ± 1/4"

## SPECIAL FEATURES:

NONE

<b>A P P R O V A L</b>	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN & DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT & INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS & STANDARDS.	
	<b>ALL SPECIAL UNITS ARE NON-RETURNABLE</b>	
	( ) As drawn      ( ) As marked	
	Signed: _____ Date: _____	
LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING		

Any additions, deletions or omissions must be corrected on this drawing, as this drawing will be considered all inclusive.	DISTRIBUTOR'S NAME: <b>VESTIL MFG</b>		P.O.#: _
	DRAWN BY: _____		W.O.#: _
All graphics provided are for reference only. If certain dimensions are critical please verify those dimensions with your salesperson	DATE: _	SALES: _	DRWG./FILE NAME: 24-007-051-102
	REFERENCE: _	SCALE: _	
	QUOTED LEADTIME: _	QUOTE #: _	