



- ✓ **Easy to Use**  
Smooth sliding headpiece and telescoping rod allows the user to quickly and easily read the height measurement.
- ✓ **Durable Construction**  
Aluminum height rod withstands frequent use. Rigorous laboratory tests showed that the Health o meter® Professional 201HR lasts 2 ½ times longer than similar models.
- ✓ **Footpiece Positioner**  
Attached footpiece serves as a guide for heel placement and ensures accurate measurements.
- ✓ **Large Measurement Range**  
The 2" / 6cm – 90" / 230cm measuring range provides height readings for a wide range of patients.
- ✓ **Wall Mount Design**  
Installs easily and quickly with simple tools and provided hardware.



Model	Shipping Dims. (L x W x H) / Cube	Weight (LB)	UPC Code
201HR	57" x 3.5" x 3.5" / .4	3.6 lb	854896003689

### Specifications

- Measuring Range: 2" / 6cm – 90" / 230cm
- Graduation: 1/16" / 1mm
- Physical Dimensions:
  - Width: 2 ¼" / 57mm (13" / 330mm including footpiece)
  - Depth: ¾" / 19mm (1 ¾" / 44mm including spacers)
  - Height: 54" / 1370mm H (92" / 2300mm with height rod fully extended)
  - Headpiece Depth When Unfolded: 11" / 280mm
- 2 Year Warranty