



MODEL 237635 (36Wx18Dx72H) www.globalindustrial.com



1-800-645-2986

INDUSTRIAL STORAGE CABINET

ASSEMBLY INSTRUCTION



CONTENTS

REF	QTY	DESCRIPTION	REF	QTY	DESCRIPTION
1	1	LEFT SIDE BACK PANEL	H1	4	M6X19mm ROUND PHILLIP HEAD SCREW 
2	1	RIGHT SIDE BACK PANEL	H2	4	6.5mm PLATE WASHER 
3	1	LEFT SIDE PANEL	H3	4	6.5mm SPLIT WASHER 
4	1	RIGHT SIDE PANEL	H4	2	BUMPER 
5	1	INNER SUPPORT BAR	H5	16	SHELF CLIP 
6	1	OUTER SUPPORT BAR	H6	4	PLASTIC INSERT 
7	1	BASE	H7	2	KEY 
8	1	TOP	H8	4	DOOR AXIS 
9	1	LEFT DOOR	H9	4	Door Nut 
10	1	RIGHT DOOR			
11	4	SHELF			



WARNING.

- 1.USE 2 PEOPLE TO ASSEMBLE.
- 2.LAY PARTS ON SOFT SMOOTH NON-SCRATCH SURFACE.
- 3.DO NOT OVERLOAD SHELVES.
- 4.LOAD LOWER SHELF FIRST.
- 5.DO NOT CLIMB OR STAND ON SHELVES.




CONTENTS

REF	QTY	DESCRIPTION	REF	QTY	DESCRIPTION
1	1	LEFT SIDE BACK PANEL	H1	4	WESTERN ROUND BRUSH-HEAD SCREW 
2	1	RIGHT SIDE BACK PANEL	H2	4	6.5mm PLATE WASHER 
3	1	LEFT SIDE PANEL	H3	4	6.5mm SPLIT WASHER 
4	1	RIGHT SIDE PANEL	H4	2	BUMPER 
5	1	INNER SUPPORT BAR	H5	16	SHELF CLIP 
6	1	OUTER SUPPORT BAR	H6	4	PLASTIC INSERT 
7	1	BASE	H7	2	KEY 
8	1	TOP	H8	4	DOOR AXIS 
9	1	LEFT DOOR	H9	4	Door Nut 
10	1	RIGHT DOOR			
11	4	SHELF			



WARNING.


1. USE 2 PEOPLE TO ASSEMBLE.
2. LAY PARTS ON SOFT SMOOTH NON-SCRATCH SURFACE.
3. DO NOT OVERLOAD SHELVES.
4. LOAD LOWER SHELF FIRST.
5. DO NOT CLIMB OR STAND ON SHELVES.



A


SEE DETAIL A and B

1




B

1




2

SEE DETAIL C and D




C

3




D



3

4




H2


H3

H1




3




5




NOTE:
FULLY SEAT BOTTOM SHELF
EDGE BEHIND Z-CHANNELS



STAND CABINET UP.
(2 PEOPLE REQUIRED)



8



9

16- H5

SEE DETAIL F and G

