

# 400 SERIES

## COMMERCIAL KD CABINETS

2 YEAR  
WARRANTY

### Features:

- All components precision engineered with no bolt heads showing on front and side panels.
- Body and shelves fabricated from 22 gauge steel.
- Shelves easily adjust up or down in 2" increments. Triple flanged shelf front for added strength (capacity up to 200 lbs).
- Reinforced doors swing a full 180°.
- Doors are factory-hung in 16 gauge frames ensuring proper performance.
- 16 gauge continuous hinges.

### Configurations:

- Storage (includes 4 adjustable shelves)
- Wardrobe (includes 1 shelf and coat rod)
- Combination (includes 1 full width shelf, 3 half width Shelves and a half width coat rod)

- Corner foot gussets provide added rigidity and stability (replaced by mounting plates on mobile units).
- Mobile units include four heavy-duty locking swivel casters.
- Positive three-point locking (top, center and bottom) for secure locking (single cam only for 16" wide wall-mount cabinets).
- Plated locking handle has built-in cylinder key lock (keys included).

### Door Options:

- Solid
- Safety-View (includes polycarbonate panels in door)
- Ventilated (includes expanded metal panels in door)



STATIONARY COMBINATION  
SOLID DOORS



MOBILE STORAGE  
VENTILATED DOORS



STATIONARY WARDROBE  
SAFETY-VIEW DOORS



725  
DARK GRAY  
(HG)

708  
BLACK  
(ME)

729  
TAN  
(PT)

Description	Width	Depth	Height	Knock-Down Cat No.	Assembled Cat No.	Color Selection
SOLID DOOR CABINETS, 400 SERIES						
Stationary, Storage	36	18	72	415S18	415S18A	ME, HG, PT
Stationary, Storage	36	24	72	415S24	415S24A	ME, HG, PT
Stationary, Storage	48	18	72	425S18	425S18A	ME, HG, PT
Stationary, Storage	48	24	72	425S24	425S24A	ME, HG, PT
Stationary, Wardrobe	36	18	72	435W18	435W18A	ME, HG, PT
Stationary, Wardrobe	36	24	72	435W24	435W24A	ME, HG, PT
Stationary, Wardrobe	48	18	72	445W18	445W18A	ME, HG, PT
Stationary, Wardrobe	48	24	72	445W24	445W24A	ME, HG, PT
Stationary, Combination	36	18	72	455C18	455C18A	ME, HG, PT
Stationary, Combination	36	24	72	455C24	455C24A	ME, HG, PT
Stationary, Combination	48	18	72	465C18	465C18A	ME, HG, PT
Stationary, Combination	48	24	72	465C24	465C24A	ME, HG, PT
Mobile, Storage	36	24	72	415S24M	415S24MA	ME, HG, PT
Mobile, Storage	48	24	72	425S24M	425S24MA	ME, HG, PT
SAFETY VIEW DOOR CABINETS, 400 SERIES						
Stationary, Storage	36	18	72	415S18SV	415S18SVA	ME, HG, PT
Stationary, Storage	36	24	72	415S24SV	415S24SVA	ME, HG, PT
Stationary, Storage	48	18	72	425S18SV	425S18SVA	ME, HG, PT
Stationary, Storage	48	24	72	425S24SV	425S24SVA	ME, HG, PT
Stationary, Wardrobe	36	18	72	435W18SV	435W18SVA	ME, HG, PT
Stationary, Wardrobe	36	24	72	435W24SV	435W24SVA	ME, HG, PT
Stationary, Wardrobe	48	18	72	445W18SV	445W18SVA	ME, HG, PT
Stationary, Wardrobe	48	24	72	445W24SV	445W24SVA	ME, HG, PT
Stationary, Combination	36	18	72	455C18SV	455C18SVA	ME, HG, PT
Stationary, Combination	36	24	72	455C24SV	455C24SVA	ME, HG, PT
Stationary, Combination	48	18	72	465C18SV	465C18SVA	ME, HG, PT
Stationary, Combination	48	24	72	465C24SV	465C24SVA	ME, HG, PT
Mobile, Storage	36	24	72	415S24SVM	415S24SVMA	ME, HG, PT
Mobile, Storage	48	24	72	425S24SVM	425S24SVMA	ME, HG, PT
VENTILATED DOOR CABINETS, 400 SERIES						
Stationary, Storage	36	18	72	415S18EV	415S18EVA	ME, HG, PT
Stationary, Storage	36	24	72	415S24EV	415S24EVA	ME, HG, PT
Stationary, Storage	48	18	72	425S18EV	425S18EVA	ME, HG, PT
Stationary, Storage	48	24	72	425S24EV	425S24EVA	ME, HG, PT
Stationary, Wardrobe	36	18	72	435W18EV	435W18EVA	ME, HG, PT
Stationary, Wardrobe	36	24	72	435W24EV	435W24EVA	ME, HG, PT
Stationary, Wardrobe	48	18	72	445W18EV	445W18EVA	ME, HG, PT
Stationary, Wardrobe	48	24	72	445W24EV	445W24EVA	ME, HG, PT
Stationary, Combination	36	18	72	455C18EV	455C18EVA	ME, HG, PT
Stationary, Combination	36	24	72	455C24EV	455C24EVA	ME, HG, PT
Stationary, Combination	48	18	72	465C18EV	465C18EVA	ME, HG, PT
Stationary, Combination	48	24	72	465C24EV	465C24EVA	ME, HG, PT
Mobile, Storage	36	24	72	415S24EVM	415S24EVMA	ME, HG, PT
Mobile, Storage	48	24	72	425S24EVM	425S24EVMA	ME, HG, PT

## 405 SERIES COMMERCIAL WALL MOUNT KD CABINETS

### FEATURES:

- All components precision engineered with no bolt heads showing on front and side panels.
- All components fabricated from 22 gauge steel.
- Plated locking handle has built-in cylinder key lock (keys included).
- Shelves easily adjust up or down in 2" increments.



725  
DARK GRAY  
(HG)

708  
BLACK  
(ME)

729  
TAN  
(PT)

WALL MOUNT  
36" WIDE DOUBLE DOOR  
SAFETY-VIEW DOORS



WALL MOUNT 16" WIDE  
SINGLE SOLID DOOR



Description	Width	Depth	Height	Knock-Down Cat No.	Assembled Cat No.	Color Selection
WALL MOUNT SOLID DOOR CABINETS, 405 SERIES						
Wall Mount, Storage	16	12	26	405-1626	405-1626A	ME, HG, PT
Wall Mount, Storage	30	12	26	405-3026	405-3026A	ME, HG, PT
Wall Mount, Storage	36	12	30	405-3630	405-3630A	ME, HG, PT
WALL MOUNT SAFETY VIEW DOOR CABINETS, 405 SERIES						
Wall Mount, Storage	16	12	26	405-1626SV	405-1626SVA	ME, HG, PT
Wall Mount, Storage	30	12	26	405-3026SV	405-3026SVA	ME, HG, PT
Wall Mount, Storage	36	12	30	405-3630SV	405-3630SVA	ME, HG, PT