



LOW PROFILE - DUMPING HOPPER BASIC DIMENSIONS

CAPACITY	PART NUMBER	OVER ALL WIDTH	OVER ALL HEIGHT	OVER ALL LENGTH	FORK OPENING	POURING LIP	CONTAINER LENGTH	DUMP CLEARANCE HEIGHT	DUMP CLEARANCE BOTTOM	DUMP CLEARANCE LENGTH	FRONT CLEARANCE	BASE WIDTH	BASE LENGTH	DUMP ANGLE	CENTER of GRAVITY	WEIGHT CAPACITY	APPROX. WEIGHT
		(A)	(B)	(C)	(D)	(E)	(F)	(G)	(H)	(I)	(J)	(K)	(L)	(M)	(N)		
1/4 cu yd	988856	31"	17"	43"	2" by 22"	0"	33 5/8"	38 1/2"	18 1/2"	37 3/4"	20 3/4"	22 3/8"	22 1/4"	90°	23"	4000 lb.	193 lb.
1/3 cu yd	988857	41"	17"	43"	2" by 28"	0"	33 5/8"	38 1/2"	18 1/2"	37 3/4"	20 3/4"	28 3/8"	22 1/4"	90°	23"	4000 lb.	238 lb.
1/2 cu yd	988858	62"	17"	43"	2" by 28"	0"	33 5/8"	38 1/2"	18 1/2"	37 3/4"	20 3/4"	28 3/8"	22 1/4"	90°	23"	4000 lb.	287 lb.
3/4 cu yd	988859	48 1/2"	24"	55 3/4"	2" by 28"	0"	48 1/4"	51 1/4"	27 1/2"	48 1/2"	30"	28 3/8"	25 3/4"	90°	28 1/8"	5000 lb.	455 lb.
1 cu yd	988860	63 1/2"	24"	55 3/4"	2" by 28"	0"	48 1/4"	51 1/4"	27 1/2"	48 1/2"	30"	28 3/8"	25 3/4"	90°	28 1/8"	5000 lb.	515 lb.
1 1/2 cu yd	988861	62"	24"	75"	2" by 48"	0"	67"	69"	36"	58"	38 1/2"	42"	36"	90°	36 1/2"	5000 lb.	685 lb.

Item # 988856, 988857, 988858 1/8" Steel (11 Gauge) Hopper with 3/16" (7 Gauge) Steel Base

Item # 988859, 988860, 988861 3/16" Steel (7 Gauge) Hopper with 3/16" (7 Gauge) Steel Base

Note: All dimensions are approximate some dimensions may vary slightly per hopper.