

Portable extractors with deep-cleaning power, built-in convenience and productivity

ET610™ portable extractors are the culmination of a major engineering and design initiative of Advance that emanated from direct field input of cleaning technicians who used high performance portable extraction machines every day.

The ET610 represents a dramatic step forward in implementing unique, productivity enhancing features that considered even the minutest detail. These features go a step beyond traditional componentry that is common to most extractors – pumps and vacuum motors – and take into account the most common annoyances expressed by cleaning technicians. For example, moving the solution tank filling site to a location where the inevitable spill does not come in contact with any electrical components or switches. The ET610 has a 3-stage vacuum motor for unrestricted airflow and superior water recovery. The closed, sealed system reduces wear and extends vacuum motor life. A pressure gauge, pressure regulator allows you to dial in specific pressure for sensitive texture, hard and textile surfaces. Extension cord wraps protect cords and make maneuverability and transport through facilities easier. No detail was overlooked.

- 12.5 gallon solution tank
- 11 gallon recovery tank
- Two handles for easy maneuverability
- Handle on tank to assist loading/ unloading and to guide vacuum hose
- Oversized, rubber grip rear wheels
- Easy-fill solution tank access port

• Standard equipment

Included accessories	Ref. no.	Min. required	ET610 100H	ET610 100H-15-SW	ET610 100C-15-SW
Vacuum Hose and Connection					
VAC HOSE/PRESSURE LN. 15 EXTR	FP153	0	•	•	•


• Standard equipment

Included accessories	Ref. no.	Min. required	ET610 100C
Vacuum Hose and Connection			
VAC HOSE/PRESSURE LN. 15 EXTR	FP153	0	•

Model	ET610 100H	ET610 100H-15-SW	ET610 100C-15-SW
Ref. no.	56105293	56105423	56105420

PRODUCT FEATURES

Heater	•	•	•
Easy-to-carry handle	•	•	•
Wand caddy	•	•	•
Ergonomic Design	•	•	•
Two Handles for Easy Maneuverability	•	•	•
Recessed electric switch plate	•	•	•
Two Front panel Roller Wheels	•	•	•



Picture shown may not represent model quoted

Portable extractors with deep-cleaning power, built-in convenience and productivity

Model	ET610 100H	ET610 100H-15-SW	ET610 100C-15-SW
Ref. no.	56105293	56105423	56105420

PRODUCT FEATURES

Oversized, rubber grip rear wheels	•	•	•
Easy-fill Solution Tank Access Port	•	•	•
Easy-to-service Clamshell Design	•	•	•

Model	ET610 100C
Ref. no.	56105292

PRODUCT FEATURES

Heater	•
Easy-to-carry handle	•
Wand caddy	•
Ergonomic Design	•
Two Handles for Easy Maneuverability	•
Recessed electric switch plate	•
Two Front panel Roller Wheels	•
Oversized, rubber grip rear wheels	•
Easy-fill Solution Tank Access Port	•
Easy-to-service Clamshell Design	•

Technical specifications	ET610 100H	ET610 100H-15-SW	ET610 100C-15-SW
Pump	Diaphragm pump	Diaphragm pump	Diaphragm pump
Vacuum	Single 5.7 in, 3-stage	Single 5.7 in, 3-stage	Single 5.7 in, 3-stage
Weight (lbs)	87 lb	87 lb	87 lb
Dimensions L x W x H	40.5 in x 21 in x 42 in	40.5 in x 21 in x 42 in	40.5 in x 21 in x 42 in
Vac shutoff	Ball float	Ball float	Ball float
Power cord - type	Dual	Dual	Single
Heat	Yes	Yes	N/A
Pressure gauge	N/A	N/A	N/A
Waterlift/Airflow	140 in	140 in	None
Heater	1,750 W	1,750 W	N/A
Wand	12 in stainless steel scrub wand (AquaWand™ optional upgrade)	12 in stainless steel scrub wand (AquaWand™ optional upgrade)	12 in stainless steel scrub wand (AquaWand™ optional upgrade)
CRI certified	Bronze	Bronze	None




Portable extractors with deep-cleaning power, built-in convenience and productivity

Technical specifications

ET610 100C

Pump	Diaphragm pump
Vacuum	Single 5.7 in, 3-stage
Weight (lbs)	87 lb
Dimensions L x W x H	40.5 in x 21 in x 42 in
Vac shutoff	Ball float
Power cord - type	Single
Heat	N/A
Pressure gauge	N/A
Waterlift/Airflow	None
Heater	N/A
Wand	12 in stainless steel scrub wand (AquaWand™ optional upgrade)
CRI certified	None


● Standard equipment, ○ Supplementary accessories, □ Mountable equipment

Accessories	Ref. no.	Min. required	ET610 100H	ET610 100H-15-SW	ET610 100C-15-SW
Vacuum Hose and Connection					
VAC HOSE/PRESSURE LN. 15 EXTR	FP153	0	●	●	●
VAC HOSE/PRESSURE LN. 25 1/8	FP195	0	○	○	○
VAC HOSE/PRESSURE LN. 25 EXTE	FP196	0	○	○	○
Accessory					
EXTRACTOR HAND TOOL	56102807	0	○	○	○
MINI TURBO HARD SURFACE TOOL	HFT-43	0	○	○	○
TOOL 3-1/2 CLOSED DETAIL BEXT	52514A	0	○	○	○
TURBO HARD SURFACE TOOL COMPL	HFT-40	0	○	○	○
Extension Tube					
 CARPET SCRUB WAND 12HEAD-HP	CSW-12HP	0	○	○	○
CARPET SCRUB WAND 12HEAD-LP	CSW-12	0	○	○	○
Bag					
BAG W/HANDLE BLACK MESH	54084A	0	○	○	○



Portable extractors with deep-cleaning power, built-in convenience and productivity

● Standard equipment, ○ Supplementary accessories, □ Mountable equipment

Accessories		Ref. no.	Min. required	ET610 100C
Vacuum Hose and Connection				
	VAC HOSE/PRESSURE LN. 15 EXTR	FP153	0	●
	VAC HOSE/PRESSURE LN. 25 1/8	FP195	0	○
	VAC HOSE/PRESSURE LN. 25 EXTE	FP196	0	○
Accessory				
	EXTRACTOR HAND TOOL	56102807	0	○
	MINI TURBO HARD SURFACE TOOL	HFT-43	0	○
	TOOL 3-1/2 CLOSED DETAIL BEXT	52514A	0	○
	TURBO HARD SURFACE TOOL COMPL	HFT-40	0	○
Extension Tube				
	CARPET SCRUB WAND 12HEAD-HP	CSW-12HP	0	○
	CARPET SCRUB WAND 12HEAD-LP	CSW-12	0	○
Bag				
	BAG W/HANDLE BLACK MESH	54084A	0	○