

# BALLYPAL35TSL157



Straddle Leg Walkie Electric Stacker

## 3500 lbs

### SPECIFICATIONS

- Capacity= 3500 lbs.
- Weight= 3263 lbs.
- Lift Height Max. = 157"
- Fork Length= 45"
- Fork Width= 4.7"
- Overall Fork Width 19 1/2" to 38" (Adjustable)
- Lowered Mast Height = 75"
- Free Lift Height= 52"
- Extended Mast Height= 176"
- Height Lowered= 2"
- Overall Length= 82"
- Overall Width= 46" to 58"
- Travel Speed = 3.5/ 3.7 mph
- Max Gradeability= 6% Laden and 12% Unladen
- Battery Voltage 24V /2705Ah

### FEATURES

- Proportional lifting allows for efficient and safe lifting of any product at any lift speed.
- State of the art components
- Mesh Protection for safety as well as great visibility during operation
- Robust Chassis and thick apron protect the truck and its components
- Three Stage Mast



#### Straddle Leg

Adjustable straddle leg design, suitable for diverse pallet sizes and more stability



BALLYMORE COMPANY  
501 GUNNARD CARLSON DR.  
COATESVILLE, PA 19320

WWW.BALLYMORE.COM  
1-800-762-8327