

BALLYPAL

BALLYPAL22AG63



Semi Electric Stacker with Adjustable Base Legs.
Single Mast with a Lift Height of 63"

2200 lbs



SPECIFICATIONS

- Capacity= 2200 lbs.
- Lift Height Max. = 63"
- Lift Height Min. = 2 1/8"
- Fork Length= 42"
- Fork Width= 4"
- Base Legs (OD)= 46" to 58"
- Overall Length= 66 1/2"
- Overall Width= 46" to 58"
- Overall Height= 80"
- Single Mast
- Weight= 830 lbs.
- 1 Battery = 12V/150Ah

FEATURES

- Forks adjust from side to side to accommodate skid widths
- Adjustable forks lower to the minimum height 2 1/8"
- Overall fork width 8 1/4" to 28 1/2" (Adjustable)
- Straddle Legs adjust to three positions
- Sturdy mast made of rolled U- shapes
- Powerful lift motor 2.1 HP
- Battery Gauge and On/Off Switch
- Integrated 150 Ah maintenance free battery provides more than enough power to handle heavy duty lifting
- Integrated Charger facilitates easy and reliable charging



BALLYMORE COMPANY
501 GUNNARD CARLSON DR.
COATESVILLE, PA 19320

WWW.BALLYMORE.COM
1-800-762-8327