

CT66WADA



32.38" x 23.63" x 23.5" (H x W x D)

Freestanding ADA compliant refrigerator-freezer for general purpose use, with dual evaporator cooling, cycle defrost, and white exterior

Highlights:

32" height for use in ADA compliant settings

Improved temperature performance with our unique dual evaporator cooling

Over 5 cu.ft. of storage capacity in a perfectly sized 24" footprint

Product Features:

ADA Compliant	32" height for use in settings complying with ADA guidelines for lower counter height
Slim counter height dimensions	Less than 24 inches wide, with a generous 5.1 c.f. of interior capacity
Fully finished white cabinet	Allows the unit to be used freestanding
Reversible door	User-reversible door swing for added flexibility
Dual evaporator cooling	Our unique and efficient design separately cools the refrigerator while maintaining a lower temperature in the freezer compartment by utilizing two evaporators
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Adjustable shelves	Rearrange the refrigerator space to fit any sized item or remove shelves for simple cleanup
Crisper drawer	Get the longest life and best taste out of produce by storing greens in lower slide drawer
Door shelves	Store large bottles right on the door for easy access

CT66WADA Specifications:

Overview	
Height of Cabinet	32.0" (81 cm)
Height to Hinge Cap	32.38" (82 cm)
Width	23.63" (60 cm)
Depth	23.5" (60 cm)
Depth with Handle	24.13" (61 cm)
Depth with door at 90°	45.13" (115 cm)
Capacity	5.1 cu.ft. (144 L)
Defrost Type	Cycle
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.2
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs. (45 kg)
Shipping Weight	105.0 lbs. (48 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Interior Light	Yes
Refrigerator - Interior Height	19.5" (50 cm)
Refrigerator - Interior Width	20.5" (52 cm)
Refrigerator - Interior Depth	17.0" (43 cm)
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0" (13 cm)
Freezer - Interior Width	19.0" (48 cm)
Freezer - Interior Depth	11.5" (29 cm)

Thermostat Type	Dial
Refrigerant Type	R600a
Refrigerant Amount	0.92 oz.
High Side PSI	180.0
Low Side PSI	80.0
Level Legs	4
Compressor Step Height	7.0" (18 cm)
Compressor Step Width	20.5" (52 cm)
Compressor Step Depth	5.0" (13 cm)

