



# DW18SS4



34.25" x 17.75" x 22.38" (H x W x D)

18" wide ENERGY STAR certified built-in dishwasher made in Europe with stainless steel door and front controls

### Highlights:

ENERGY STAR qualified performance to save on electricity and water usage

Just under 18" wide for an easy fit in space-challenged kitchens

Stainless steel door offers a professional look

### Product Features:

ENERGY STAR certified	Uses less energy and water than national standards require to ensure more efficiency and lower utility bills
Digital touch controls	Intuitive touch button controls and LED display screen for easy use, with a program key printed on the control panel for added convenience
Front control panel	Easy access with touch control buttons
Stainless steel door	Attractive finish in durable stainless steel with a horizontal grain
Height adjustable	Adjustable legs allow you to size the unit for the best fit, with a height range of 33.5" to 35"
Ultra quiet performance	Advanced sound absorbing construction
Large capacity	Interior holds up to 8 standard place settings
Stainless steel interior	Durable interior ensures long-lasting use
Slide-out nylon coated wire racks	Two easy-gliding racks for easy loading and long-lasting durability



## DW18SS4 Specifications:

Overview	
Height of Cabinet	34.25" (87 cm)
Width	17.75" (45 cm)
Depth	22.38" (57 cm)
Depth with door at 90°	45.5" (116 cm)
Dishwasher	Standard
Door	Stainless Steel
Cabinet	Unfinished
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	220.0kWh/year
Amps	12.0
Voltage/Frequency	115 V AC/60 Hz
Weight	95.0 lbs. (43 kg)
Shipping Weight	98.0 lbs. (44 kg)
Estimated Time to Ship	Next day shipping
Parts & Labor Warranty	1 Year
Dishwasher	
Number of Cycles	5
Number of Racks	2
Rack Material	Wire
Silverware Basket	Yes
Delayed Start	Yes
Interior Finish	Stainless Steel
Interior Height	24.0" (61 cm)
Interior Width	15.25" (39 cm)
Interior Depth	20.0" (51 cm)
Decibel Rating	49.0 dBA
Number of Options	5
Place Settings	8

