

MLRS6MC



32.5" x 23.38" x 24.38" (H x W x D)

ADA height all-refrigerator for breast milk storage with 4 adjustable shelves

Highlights:

Ideal for work environments and offices complying with Section 4207 of the Patient Protection and Affordable Care Act

Perfect for employee wellness rooms, daycare centers, and lactation lounges

Preset temperature range as recommended by the CDC for mother's milk storage

Product Features:

Easy to use	User-friendly design ensures effortless use for mothers and facility managers alike
CDC-compliant temperature	Preset temperature remains within recommended range for mother's milk storage
Adjustable wire shelves	Multiple shelf positions spaced at 1/2" for improved air circulation and storage
ADA compatible height	Sized at 32.5 inches high for freestanding use with most ADA compliant applications
Sealed cabinet design	Allows for unit to be freestanding
Door lock	Added security on the exterior door (2 keys included)
Reversible door	Provides flexibility in product placement
LED display	Allows for easy reading of unit temperature
Power loss alarm	Alerts when unit loses power; NOTE: Alarm is battery-powered and has a limited time to alarm

MLRS6MC Specifications:

Overview	
Height of Cabinet	32.5" (83 cm)
Width	23.38" (59 cm)
Width with Door Open	23.88" (61 cm)
Depth	24.38" (62 cm)
Depth with Handle	26.13" (66 cm)
Depth with door at 90°	46.5" (118 cm)
Capacity	6.0 cu.ft. (170 L)
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	0.75
Voltage/Frequency	115 V AC/60 Hz
Weight	120.0 lbs. (54 kg)
Shipping Weight	130.0 lbs. (59 kg)
Estimated Time to Ship	3 to 5 days
Parts & Labor Warranty	2 Years
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Wire
Shelf Qty	4
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	1.66oz.
Interior Light	Yes
Temperature Range	33 to 40°F
Dimensions	
Interior Height	24.5" (62 cm)
Interior Width	20.0" (51 cm)
Interior Depth	17.0" (43 cm)
Compressor Step Height	6.5" (17 cm)
Compressor Step Width	20.0" (51 cm)

Compressor Step Depth 5.0"



