# accucold

# **SPRF86M2**



### **Product Features:**

25.88" x 22" x 17.5" (H x W x D)

Portable 12V/24V cooler capable of operation as refrigerator (2-8°C) or freezer (-12°C), with insulated cover, interior wire basket, factory-installed lock, strap handle, and four pre-installed wheels

#### **Highlights:**

Portable 12V/24V cooler with sturdy handles for easy carrying

Can operate as a refrigerator (2-8°C) or freezer (-12°C) for storage of medical supplies

Four pre-installed wheels and strap handle ensures userfriendly portability for added convenience

Refrigerator/freezer operation	Operates as a refrigerator (2-8°C) or freezer (-12°C) for unparalleled storage flexibility including samples, vaccines, cold packs, and other healthcare supplies (Note: If operating as a freezer, vaccine storage is not recommended.)	
12V/24V DC hookup	Plug into the lighter socket of any vehicle or 24V battery	
Portable design	Four pre-installed wheels for smooth mobility when transporting materials	
Strap handle	Side handle makes it easier to steer or pull the unit as needed	
Side handles	Sturdy handles are easy to grab for comfortable lifting and carrying	
AC Adapter included	We provide an AC adapter for users to plug the unit into a standard 110-120V wall socket for stationary use	
Digital thermostat	Easy temperature control with electronic buttons and an external thermometer readout	
Insulated cover	Insulated fabric cover helps to preserve interior temperature as well as protect the exterior cabinet	
Factory-installed lock	Provides added security with two keys included	

SUMMIT APPLIANCE DIVISION, FELIX STORCH, INC. | ISO 9001:2015 Certified 770 Garrison Avenue Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

info@summitappliance.com  $\checkmark$ 



# accucold

## SPRF86M2 Specifications:

Overview	
Height of Cabinet	25.88" (66 cm)
Width	22.0" (56 cm)
Depth	17.5" (44 cm)
Depth with Handle	18.63" (47 cm)
Capacity	2.8 cu.ft. (79 L)
Defrost Type	Manual
Door	Gray
Cabinet	Gray
Amps	4.6
Voltage/Frequency	115 V AC/60 Hz
Weight	65.0 lbs. (29 kg)
Shipping Weight	71.0 lbs. (32 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	Lift-Up
Refrigerator - Interior Height	16.25" (41 cm)
Refrigerator - Interior Width	13.25" (34 cm)
Refrigerator - Interior Depth	14.0" (36 cm)
Refrigerator - Temperature Range	2-8°C
Refrigerator - Refrigerant Type	R134a
Thermostat Type	Digital
Refrigerant Type	R134a
Refrigerant Amount	2.22 oz.
High Side PSI	212.05
Low Side PSI	16.68
	4
Wheels	-
Wheels Condensor Location	Side of Unit
	Side of Unit down to -12°C
Condensor Location Freezer - Temperature	
Condensor Location Freezer - Temperature Range	down to -12°C



